

Product data sheet

Characteristics

GV2G245

Linergy FT, Comb busbar, 63A, 2 tap-offs, 45mm pitch



Product availability: Stock - Normally stocked in distribution facility

Price*: 23.30 USD



Main

Range	Linergy
Product name	FT
Device short name	GV2G
Product or Component Type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys Deca TeSys U
Number of tap-offs	2
[I _{th}] conventional free air thermal current	63 A
Connection pitch	1.77 In (45 mm)

Complementary

Mounting Location	On terminal
[U _i] Rated Insulation Voltage	690 V
Length	3.50 In (89 mm)
Net Weight	0.08 Lb(US) (0.036 kg)

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0I11
GTIN	3389110555950
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 In (2 cm)
Package 1 Width	1.57 In (4 cm)
Package 1 Length	3.74 In (9.5 cm)
Package 1 Weight	1.31 Oz (37 g)
Unit Type of Package 2	S01
Number of Units in Package 2	100
Package 2 Height	5.91 In (15 cm)
Package 2 Width	5.91 In (15 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	8.51 Lb(US) (3.862 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	3200
Package 3 Height	30.31 In (77 cm)
Package 3 Width	31.50 In (80 cm)
Package 3 Length	23.62 In (60 cm)
Package 3 Weight	288.59 Lb(US) (130.9 kg)


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information


Contractual warranty

Warranty	18 months
----------	-----------

Sets of Busbars GV2G... with Terminal Block GV1G09



Sets of Busbars GV2G245, GV2G254, GV2GR272



	l
GV2G245 (2 x 45 mm)	89
GV2G254 (2 x 54 mm)	98
GV2G272 (2 x 72 mm)	116

Product Life Status : **Commercialised**