

*“Easy9’s quality and reliability  
make me more productive”*


New, robust equipment  
from a brand you can trust.

The new Easy9 range better supports your business as an electrician, helping you to be more effective through:

- > A high-quality, user-friendly design
- > Availability when and where you look for it
- > High reliability at a price you can afford

Proven quality at a great price.

You won't find a more reliable and affordable switchboard equipment than Easy9, and now you can take pride in bringing to your customers the enhanced safety they deserve.



Make the most of your energy<sup>SM</sup>

Schneider Electric Industries SAS

**Head Office**  
35 rue Joseph Monier  
92500 Rueil Malmaison Cedex - France  
Tel.: +33 (0)1 41 29 70 00  
[www.schneider-electric.com](http://www.schneider-electric.com)

©2014 Schneider Electric Industries SAS, All Rights Reserved. Schneider Electric, Make the most of your energy, are owned by Schneider Electric, or its affiliated companies in the United States and other countries. All other trademarks are property of their respective owners.

998-1183266\_GMA-GB

# Easy9

Affordable protection  
you can depend on



**Schneider**  
 **Electric**

## Just what you want for your switchboards



### Quality

- 100% designed and manufactured by Schneider Electric
- All sites with ISO 9000 certification
- Brand selected everywhere for industry, hospitals, airports



### Availability

- Always on the shelf at your dealer's
- Complete coverage of protection features
- Large assortment of ratings



### Customer satisfaction

- Highly reliable and safe switchboards
- Dependable power supply



### Safety

- Protection from electric shocks, overloads, short circuits, and power surges
- Compliance to standards set by state authorities



### Time saving

- Consistent design and connection features
- One-stop shopping for all parts
- Proven robustness to withstand wear and tear

**Since  
1920**  
Leader in electrical  
switchgear



### MCB 3000

Miniature circuit-breakers  
3000 Amp short-circuit breaking cap.  
1 to 3 poles  
2 to 63 A current ratings  
B and C tripping curves

### SPD

Surge protection devices  
2 to 4 poles  
Max discharge capacity: 20 kA

### MCB 4500

Miniature circuit-breakers  
4500 Amp short-circuit breaking cap.  
1 to 3 poles  
70 to 125 A current ratings  
C tripping curve

### Connection

Comb busbars  
1 to 3 poles  
80 A current rating

### RCCB

Residual-current circuit-breakers  
2 and 4 poles  
30, 100, 300 mA sensitivities  
25, 40, 63 1 current ratings

### Enclosures

Switchboard housing  
1 to 3 rows  
8 to 18 module widths



Quality approval  
from a certified  
state authority.



**Schneider**  
*Electric*

The global specialist in energy  
management. Established  
as a circuit breaker designer  
and manufacturer since 1920  
in France, today we are the  
worldwide leader of electrical  
protection technologies present  
in more than 100 countries.