

Dexson Plastic Cable Mgmt system -Accesorios

External Elbow

DXN11021E, DXN11041E, DXN11171, DXN11051E, DXN11061E, DXN11071E, DXN11191, DXN11081E, DXN11091E, DXN11101E, DXN11011E, DXN11031E, DXN11171E, **DXN11181E***, DXN11171E.

Internal Elbow

DXN11022E, DXN11042E, DXN11182, DXN11052E, DXN11062E, DXN11072E, DXN11202, DXN11082E, DXN11092E, DXN11102E, DXN11012E, DXN11032E, DXN11182E, **DXN11192E***, DXN11182E.

Flat Elbow

DXN11023E, DXN11043E, DXN11203, DXN11053E, DXN11063E, DXN11073E, DXN11223, DXN11083E, DXN11093E, DXN11103E, DXN11013E, DXN11033E, DXN11203E, DXN11213E, **DXN11203E***.

Cover

DXN11025E, DXN11045E, DXN11216, DXN11055E, DXN11065E, DXN11075E, DXN11226, DXN11085E, DXN11095E, DXN11105E, DXN11015E, DXN11035E, DXN11175E, **DXN11185E***, DXN11175E.

Cover Clip

DXN11026E, DXN11046E, DXN11216, DXN11056E, DXN11066E, DXN11076E, DXN11206, DXN11086E, DXN11096E, DXN11106E, DXN11016E, DXN11036E, DXN11216E, **DXN11226E***, DXN11216E.

Tee

DXN11024E, DXN11044E, DXN11019, DXN11054E, DXN11064E, DXN11074E, DXN11020, DXN11084E, DXN11094E, DXN11104E, DXN11014E, DXN11034E, DXN11019E, **DXN11020E***, DXN11019E.



External Elbow



Internal Elbow



Flat



Cover Clip



Cover



Tee

***For DXN on bold font**



Technical Features

- ✓ With compartments for separating different cables types (apply only for 40x12 and 32x12 references).
- ✓ Stainless
- ✓ Offer aesthetic design finishes.
- ✓ Suitable for optic fiber, cat 5e & 6
- ✓ IEC 61084 standard for specific references and Fire Reaction standard with classification M1 for ABS-PC raw material.

Product Description

Image	Type	Color	Dimensions W/H/D(mm)		Commercial Ref.	Description
			W	H		
	For 10x10 Cable Mgmt system	White	24	24	DXN11021/E	External Elbow W 10x10
	For 20x12 Cable Mgmt system	White	21.5	30	DXN11041/E	External Elbow W 20x12
	For 22x10 Cable Mgmt system	White	30	25.5	DXN11171	External Elbow W 22x10
	For 20x20 Cable Mgmt system	White	46.1	46.1	DXN11051/E	External Elbow W 20x20
	For 25x25 Cable Mgmt system	White	70.5	70.5	DXN11061/E	External Elbow W 25x25
	For 32x12 Cable Mgmt system	White	54	54	DXN11071/E	External Elbow W 32x12
	For 40x12 Cable Mgmt system	White	40.6	42.6	DXN11191	External Elbow W 40x12
	For 40x25 Cable Mgmt system	White	83	83	DXN11081/E	External Elbow W 40x25
	For 40x40 Cable Mgmt system	White	85.5	85.5	DXN11091/E	External Elbow W 40x40
	For 60x40 Cable Mgmt system	White	89.8	89.8	DXN11101/E	External Elbow W 60x40
For 100x45 Cable Mgmt system	White	113	113	DXN11011/E	External Elbow W 100x45	
	For 10x10 Cable Mgmt system	White	23.9	23.9	DXN11022/E	Internal Elbow W 10x10
	For 20x12 Cable Mgmt system	White	22.8	29.9	DXN11042/E	Internal Elbow W 20x12
	For 22x10 Cable Mgmt system	White	30	25.5	DXN11182	Internal Elbow W 22x10
	For 20x20 Cable Mgmt system	White	45.7	45.7	DXN11052/E	Internal Elbow W 20x20
	For 25x25 Cable Mgmt system	White	55	55	DXN11062/E	Internal Elbow W 25x25
	For 32x12 Cable Mgmt system	White	34.8	34.8	DXN11072/E	Internal Elbow W 32x12
	For 40x12 Cable Mgmt system	White	45	43	DXN11202	Internal Elbow W 40x12
	For 40x25 Cable Mgmt system	White	61.8	61.8	DXN11082/E	Internal Elbow W 40x25
	For 40x40 Cable Mgmt system	White	75	75	DXN11092/E	Internal Elbow W 40x40
	For 60x40 Cable Mgmt system	White	76	76	DXN11102/E	Internal Elbow W 60x40
For 100x45 Cable Mgmt system	White	89.4	89.4	DXN11012/E	Internal Elbow W 100x45	

	For 10x10 Cable Mgmt system	White	22.9	22.9		DXN11023/E	Flat Elbow W 10x10
	For 20x12 Cable Mgmt system	White	39.7	39.7		DXN11043/E	Flat Elbow W 20x12
	For 22x10 Cable Mgmt system	White	42.2	11.1		DXN11203	Flat Elbow W 22x10
	For 20x20 Cable Mgmt system	White	45.2	45.2		DXN11053/E	Flat Elbow W 20x20
	For 25x25 Cable Mgmt system	White	53.5	53.5		DXN11063/E	Flat Elbow W 25x25
	For 32x12 Cable Mgmt system	White	55	55		DXN11073/E	Flat Elbow W 32x12
	For 40x12 Cable Mgmt system	White	70	13.3		DXN11223	Flat Elbow W 40x12
	For 40x25 Cable Mgmt system	White	78.7	78.7		DXN11083/E	Flat Elbow W 40x25
	For 40x40 Cable Mgmt system	White	71.3	71.3		DXN11093/E	Flat Elbow W 40x40
	For 60x40 Cable Mgmt system	White	80.2	80.2		DXN11103/E	Flat Elbow W 60x40
	For 100x45 Cable Mgmt system	White	153	153		DXN11013/E	Flat Elbow W 100x45
	For 10x10 Cable Mgmt system	White	12.8	10.7		DXN11025/E	Cover W 10x10
	For 20x12 Cable Mgmt system	White	21.6	13.9		DXN11045/E	Cover W 20x12
	For 22x10 Cable Mgmt system	White	22.3	11.1		DXN11216	Cover W 22x10
	For 20x20 Cable Mgmt system	White	22.8	21.4		DXN11055/E	Cover W 20x20
	For 25x25 Cable Mgmt system	White	27.5	27.5		DXN11065/E	Cover W 25x25
	For 32x12 Cable Mgmt system	White	34.2	13.4		DXN11075/E	Cover W 32x12
	For 40x12 Cable Mgmt system	White	42.3	13.5		DXN11226	Cover W 40x12
	For 40x25 Cable Mgmt system	White	43	25		DXN11085/E	Cover W 40x25
	For 40x40 Cable Mgmt system	White	41.5	43		DXN11095/E	Cover W 40x40
	For 60x40 Cable Mgmt system	White	64.2	41.6		DXN11105/E	Cover W 60x40
	For 100x45 Cable Mgmt system	White	105.4	22		DXN11015/E	Cover W 100x45
	For 10x10 Cable Mgmt system	White	12.9	13.95		DXN11026/E	Cover clip W 10x10
	For 20x12 Cable Mgmt system	White	23.2	21		DXN11046/E	Cover clip W 20x12
	For 22x10 Cable Mgmt system	White	24.3	11.1		DXN11216	Cover clip W 22x10
	For 20x20 Cable Mgmt system	White	23.1	21.8		DXN11056/E	Cover clip W 20x20
	For 25x25 Cable Mgmt system	White	25	27		DXN11066/E	Cover clip W 25x25
	For 32x12 Cable Mgmt system	White	33.5	21		DXN11076/E	Cover clip W 32x12
	For 40x12 Cable Mgmt system	White	42.3	13.5		DXN11206	Cover clip W 22x10
	For 40x25 Cable Mgmt system	White	42.3	21.7		DXN11086/E	Cover clip W 40x25
	For 40x40 Cable Mgmt system	White	40	42.5		DXN11096/E	Cover clip W 40x40
	For 60x40 Cable Mgmt system	White	63.8	29.8		DXN11106/E	Cover clip W 60x40
	For 100x45 Cable Mgmt system	White	106.2	40		DXN11016/E	Cover clip W 100x45
	For 10x10 Cable Mgmt system	White	22.9	32.9		DXN11024/E	Tee W 10x10
	For 20x12 Cable Mgmt system	White	40.6	59.7		DXN11044/E	Tee W 20x12
	For 22x10 Cable Mgmt system	White	41.5	57.9		DXN11019	Tee W 22x10
	For 20x20 Cable Mgmt system	White	45.2	68		DXN11054/E	Tee W 20x20
	For 25x25 Cable Mgmt system	White	55	80		DXN11064/E	Tee W 25x25
	For 32x12 Cable Mgmt system	White	61.4	89.3		DXN11074/E	Tee W 32x12
	For 40x12 Cable Mgmt system	White	62.3	89.2		DXN11020	Tee W 40x12
	For 40x25 Cable Mgmt system	White	79	115		DXN11084/E	Tee W 40x25
	For 40x40 Cable Mgmt system	White	98.6	135.2		DXN11094/E	Tee W 40x40
	For 60x40 Cable Mgmt system	White	98.6	135.2		DXN11104/E	Tee W 60x40
	For 100x45 Cable Mgmt system	White	105.5	160.1		DXN11014/E	Tee W 100x45

Product Identification

Identification 1 (Unitary Packing)

- ✓ Bar code EAN 13.
- ✓ Product Description.
- ✓ Production employee first name letter.
- ✓ Reference.
- ✓ Production Order Number.
- ✓ Date and Hour.

- ✓ Color.
- ✓ Date and Hour.
- ✓ Production employee first name letter.
- ✓ Production Order Number.
- ✓ Net weight.
- ✓ Gross Weight.

Identification 2 (Bag):

- ✓ Bar code EAN14.
- ✓ Reference and product description.
- ✓ Packaging Unit.
- ✓ Hour.
- ✓ Production employee first name letter.
- ✓ Production Order Number.
- ✓ Net weight.
- ✓ Gross Weight.

Identification 3 (Box):

- ✓ Bar code EAN14.
- ✓ Reference and product description.
- ✓ Packaging Unit.
- ✓ Color.
- ✓ Date and