## APC Back-UPS<sup>™</sup>325



Part Number: BE325-IT

## **Battery Backup with Surge Protection for Electronics and Computers**

APC by Schneider Electric's Back-UPS 325 provides enough battery backup power so you can work through short length power outages. It also safeguards your equipment against damaging surges and spikes that travel along utility and phone lines. The Back-UPS series is "greener" than ever, using an ultra-efficient design that consumes less power during normal operation than any other battery backup in its class. This reduces your energy costs and environmental impact. Combined with all of the standard features of the Back-UPS series, the 325 is the perfect unit to protect your productivity from the constant threat of bad power and lost data.

## **Product Applications:**

All-in-one Desktop PC Home Networking (DSL-modem or wireless router) CCTV Networking Storage (NAS) POS Equipment Landline Cordless Phone





## **Product Features:**

- LED Indicator and Audible Alarms
  Quickly understand the unit and power status
  through visual and audible indicators.
- 4 battery backup and surge protected Schuko sockets
  - 2 battery backup and surge protection Keep critical electronic equipment running when the power goes out or fluctuates at dangerous levels, so you can protect your work and save your data.
  - 2 surge protection only
    Protect your secondary electronics from harmful
    surges and spikes without reducing battery capacity
    used to run primary electronics during power
    outages.
- Telephone Data Line Surge Protection
  Guards against damaging surges and spikes
  traveling over an analog phone line.
- Push Button Circuit Breaker
  Provides for easy recovery from circuit overloads
  and protects your fuse box and electronics from
  electrical damage.
- Automatic Diagnostic Testing
  Periodic battery self-test ensures early detection of a battery that needs to be replaced.
- 6 2 Yr Warranty
  APC offers a 2 year warranty with free technical phone and online support, providing customer peace of mind.



Back-UPS 325 Specifications	
Model Number	BE325-IT
Output	
Output Capacity	325 VA / 185 Watts
Output Voltage / Frequency (On utility)	230V / 50 Hz
Output Voltage / Frequency (On battery)	230V +/-8%, 47 - 63 Hz +/-1 Hz
Output Connections	4 Schuko CEE 7 outlets (2 battery backup and surge protection, 2 surge protection only)
Waveform Type	Stepped Approximation to Sine Wave
Input	
Input Voltage / Frequency	230V / 50 Hz +/- 3 Hz
Input Connection	1 x 1.8M power cord Schuko CEE 7
Surge Protection	
AC Power Surge Protection	All outlets
Data Line Surge Protection	RJ-11 phone/modem/fax/DSL protection (two wire single line)
Physical	
Unit Dimensions (W x D x H)	360 x 95 x 115 mm
Unit Weight	4.00 Kg
Shipping Dimensions (W x D x H)	465 x 116 x 153 mm
Shipping Weight	4.60 Kg
Color	Black
UPC Code	731304217039
Battery	
Battery Type	Maintenance-free, sealed lead-acid battery, leak proof
Battery Size	12 volt, 3 Ah
Management	
Alarms	Visual (LED) and audible alarms
Warranty	2 Years Repair or Replace



132 Fairgrounds Rd West Kingston, RI 02892

