Through technology perfected by research

Switches

High durability:

- Riveted moving contacts with silver inlay for proper contact
- Rocker made of high temperature resistant material

Safe and secure:

- Switches X rated for inductive loads

Sockets

Safe and secure:

- Complete range of sockets – 6A,16A, 6/16A, Universal Socket, 13A Flat Pin
- Prevents single pin insertion ensuring 'Child Proof' sockets

Hassle free Operation:

- Entry chamber for easy insertion

Fan Regulator

- 5 Distinct steps for uniform speed variation
- No RF/ EMI interference for smooth, hum free operation

Wide Range

- Switches with indicator
- Bell press switches in 1M & 2M
- Light dimmers in 400 W
- Gold plated RJ 45 socket contacts suitable for Cat 6 LAN cables
- Cover plates from 1M to 18M

Life Is On | Schneider Electric

Life Is On | Schneider Electric

schneider-electric.co.in

Ahmedabad
Schneider Electric India (P) Ltd.
42 A, 4th Floor, Space House,
Opp. Sri Krishna Centre,
Mithakali Six Roads,
Ahmedabad-380009
Tel.: 079-3940400

Bangalore
Schneider Electric India (P) Ltd.
4th floor, Electra, Wing A,
Exora Business Parks, Marathahalli
Sarjapur Outer Ring Road,
Bangalore - 560103
Tel.: 080 4333 3333

Chandigarh
Schneider Electric India (P) Ltd.
2nd Floor of Tower A
Bestech Business Tower
Sector-66
Mohali- 160059
Tel.: 0172-3324500

Chennai
Schneider Electric India (P) Ltd.
172, Poonamallee Byepass Road
Chennai- 600056.
Tel.: 91-44-30962300

Coimbatore
Schneider Electric India (P) Ltd.
No. -104, Classic Tower, 3rd Floor,
Trichy Road, Coimbatore-641018
Tel.: 0422-3940400

Jaipur
Schneider Electric India (P) Ltd.
Jaipur Business Centre 309, 3rd Floor,
Sangam Tower 190, Church Road,
Jaipur - 302001
Tel.: 0141-3912903

Kolkata
Schneider Electric (I)Pvt.Ltd,
BP-4, Sector-V
Technopolis
3rd floor, Salt Lake City
Kolkata- 700 091
Tel.: 033-333640100-101

Lucknow
Schneider Electric India (P) Ltd.
1st Floor, Asha Bhawan 27 / II -A,
Gokhale Marg, Lucknow- 226001
Tel.: 0522-4006010

Ludhiana
Schneider Electric India (P) Ltd.
Office No. - 3, 5th Floor, Novelty Plaza
Bhaiwala Chowk
Ludhiana- 140001
Tel.: 0161- 4656672-75

Mumbai
Schneider Electric India (P)(Ltd)
Marwah House, 2nd Floor
Krishanlal Marwah Marg,
Andheri (East), Mumbai - 400072
Tel.: 91-22-30263300

Nagpur
Schneider Electric India (P) Ltd.
Fortune Business Centre, 6,
Basant Vihar, W.H.C Road
Shankar Nagar, Nagpur- 440010
Tel.: 0712-2558581

Pune
Schneider Electric India (P) Ltd.
1st Floor, R.B. Business Centre
Above Dass Electronics
Sanghvi Nagar, Aundh, Pune- 411007
Tel.: 020-39404000

Secunderabad
D.No. 1-8-271, # 401, Ashoka Bhoopal Chambers, SP Road,
Secunderabad - 500003
Tel.: 04039404000
Fax.: 040-39131313

Vadodara
Schneider Electric India (P) Ltd.
Ground Floor, Vanijya BhavanRace Cource Circle
Alkapuri, Vadodara - 390007
Tel.: 0265-3940400

Vishakhapatnam
Schneider Electric India (P) Ltd.
Ratnam's Business Centre,
D.N.10-1-43, 1st Floor
Siripuram Fort,C.B.M.Compound,
Visakhapatnam- 530016
Tel.: 0891 - 2508990

Schneider Electric India Pvt. Ltd.
Corporate Office: 9th Floor, DLF Building No. 10,
Tower C, DLF Cyber City, Phase II,
Gurgaon 122002 Haryana
Tel.: ++91 124 3940400
Fax: ++91 124 4222036/ 037

Customer Care Centre
Monday - Saturday, 9 am to 8 pm
Toll-free numbers: 1800 425 4272, 1800 103 0011
Email: customercare.in@schneider-electric.com

Distributor

opale



Switches with Satin Finish

schneider-electric.co.in

Visual delight for tasteful interiors

High safety with reliable performance:

- High grade flame retardant polycarbonate
- IP 20 degree of protection

Ease of installation:

- Snap-in snap-out front loading modules
- Terminals with indented screws
- In line center terminal for continuous wiring

Style that inspires:

- Patented Satin finish
- Prevents light reflection off the surface
- Scratch resistant easy to clean surface
- Soft white color: Gels with any interior

Life Is On | Schneider Electric

X1028 WH, X1128 WH
X1286 WH, AAKX1232 WH

X1085 WH X1001 WH
X1101 WH

X2010 WH X2106 WH

X3104 WH X3200 WH

X4011 WH X4500 WH

X5002 X5001

Description	Ref Code for White	Ref Code for Coke Grey
Switches		
6A 1-way	X1001-WH	AAKY1001
6A 1-way with indicator lamp	X1081-WH	AAKY1081
6A 2-way	X1002-WH	AAKY1002
16A 1-way	X1101-WH	AAKY1101
16A 1-way with indicator lamp	X1181-WH	AAKY1181
16A 2-way	X1102-WH	AAKY1102
6A 1-way switch, 2 module	X1021-WH	AAKY1021
16A 1-way switch, 2 module	X1121-WH	AAKY1121
6A 1-way switch, 2 module, with indicator	X1028-WH	AAKY1028
16A 1-way switch, 2 module, with indicator	X1128-WH	AAKY1128
20A DP with indicator lamp	X1286-WH	AAKY1286
32A DP with indicator lamp	AAKX1232-WH	
25A Motor Starter Switch	X1186-WH	AAKY1186
6A bell push	X1005-WH	AAKY1005
6A bell push(2M size)	X1025-WH	AAKY1025
6A bell push with indicator	X1085-WH	AAKY1085
6A bell push with indicator (2M size)	X1086-WH	AAKY1086
Socket		
6A 2-pin/3-pin (shuttered)	X2005-WH	AAKY2005
6A "Uni socket" (shuttered)	X2007-WH	AAKY2007
16A 3-pin (shuttered)	X2103-WH	AAKY2103
6A/16A 3-pin (shuttered)	X2106-WH	AAKY2106
13A BS flat pin (shuttered)	X2403-WH	AAKY2403
20A 3-pin socket Outlet (shuttered)	X2206-WH	AAKY2206
25A 3-pin socket Outlet (shuttered)	X2207-WH	AAKY2207
13A multi pin socket (shuttered)	X2010-WH	AAKY2010
Dimmer/Fan Regulator		
Dimmer 400W	X3004-WH	AAKY3004
Dimmer 1200W	X3012-WH	AAKY3012
Step type fan regulator	X3200-WH	AAKY3200
Dimmer 400W in Single Module	X3104-WH	AAKY3104
Data/TV/Communication		
RJ11 (no shutter)	X4010-WH	AAKY4010
RJ11 (shuttered)	X4011-WH	AAKY4011
Twin RJ 11 (no shutters)	X4020-WH	AAKY4020
RJ 45 (shuttered)	X4045-WH	AAKY4045
TV socket	X4500-WH	AAKY4500
RJ 45 cover for key stone type	X4050-WH	AAKY4050
Gripped Cord Outlet	X4550-WH	AAKY4550
Neon Phase Indicator		
Neon phase indicator red	X5001	
Neon phase indicator green	X5002	
Neon phase indicator yellow	X5003	

Life Is On | Schneider Electric

schneider-electric.co.in

X0701 X0733

X0708

X3300 WH X0001 WH

Matt Silver

Matt Gold

DND Pro

Keytag Switch

Description	Ref Code for White	Ref Code for Coke Grey
Cover+Grid Frame		
1-2M Grid Frame & 1M Cover Frame	X0701	AAKY0801
1-2M Grid Frame & 2M Cover Frame	X0702	AAKY0802
3M Grid Frame & 3M Cover Frame	X0703	AAKY0803
3M Universal Grid Frame & 3M Universal Cover Frame	X0733	AAKY0833
4M Grid Frame & 4M Cover Frame	X0704	AAKY0804
6M Universal Grid Frame & 3M Cover Frame	X0706	AAKY0806
8M Grid Frame & 8M Cover Frame-Linear	X0708	AAKY0808
8M Grid Frame & 8M Cover Frame-Square	X0709	AAKY0809
12M Grid Frame & 12M Cover Frame	X0712	AAKY0812
18M Grid Frame & 18M Cover Frame**	AAKX0718	

**Available in White colour only

Description	Ref Code for White	Ref Code for Coke Grey
Others		
Buzzer	X3300-WH	AAKY3300
Blank off unit (1M)	X0001-WH	AAKY0001
Adoptor Plate for 30 mech series Mechanism	X0002-WH	AAKY0002

Colour Plate	Ref Code Matt Silver	Ref Code Matt Gold
1 Module Grid and Cover frame	AAKX0741	AAKX0751
2 Module Grid and Cover frame	AAKX0742	AAKX0752
3 Module Grid and Cover frame	AAKX0743	AAKX0753
3 Module Universal Grid and Cover frame	AAKX0744	AAKX0754
4 Module Grid and Cover frame	AAKX0745	AAKX0755
6 Module Grid and Cover frame	AAKX0746	AAKX0756
8 Module Grid and Cover frame-Linear	AAKX0747	AAKX0757
8 Module Grid and Cover frame-Square**	AAKX0748	AAKX0758
12 Module Grid and Cover frame**	AAKX0749	AAKX0759

**Non-stockable item. Delivery shall take four weeks.

Hotel Series	Ref Code*
DND Panel	AAKX6001
DND Switch	AAKX6002
MMR Panel	AAKX6003
MMR Switch	AAKX6004
Keytag Swith, 20A	AAKX6005
Shaver Socket++	AAKX6006

Available in white colour Only*

++Suitable Box size is X0103

Life Is On | Schneider Electric