

Kavacha Weatherproof Door Bell

- Slim surface mount faceplate features a recessed flush back makes installation easy and effective even on rough wall surfaces, without the need to open a big hole in the wall
- Large press dolly switch with Blue LED locator provides higher visibility
- Co-injection moulded gasket which seals tight with seamless polycarbonate cover plate so water can't penetrate
- Not only the door bell, it is also ideal to operate as an outdoor electric gate switch in a weather-exposed entrance
- IP44 certified



Kavacha Full-Time Weatherproof Membrane Switch Cover

- Flexible and UV-impervious membrane allows switch to be pressed easily when cover is tightly closed
- See-through membrane cover doesn't affect home décor
- Patented detachable cover can be safely unlocked for removal
- Double-injection moulded cover increases the level of protection from any moisture or dust entering
- Suitable for laundry rooms, kitchens and bathrooms
- IP55 certified



Kavacha Full-Time Weatherproof Socket Cover

- Curvy cover with spacious room for plug in various sizes to fit in and covers can still be tightly closed
- Cover can snugly click shut around the plug cord, leaving no gap
- Padlock the cover shut for added security
- Crystal-clear polycarbonate ensures interior design is uninterrupted
- Suitable for every electrical socket in your home bathrooms, laundry rooms, kitchens
- IP55 certified



Kavacha AS Switch and Socket

- Attractive large press switch dolly design which is easy to press
- Easy lifted protection shield for socket outlet allows easy access
- Protection shield and co-injected weather seal for socket outlet to ensure plug is completely kept out of water and moisture
- Balconies, swimming pools, exterior walls and gardens will all be much safer from exposed electricity
- Accept any British standard home appliance plugs
- IP66 certified for switch, IP56 certified for socket



Kavacha W Isolating Switch

- In outdoor areas for safe isolation of air conditioners and other heavy duty motorized appliances
- Impact resistant base and cover can safely withstand violent blows
- Lever is lockable in the OFF position for greater safety when routine maintenance
- Weatherproof gasket guarantees tight sealing
- Dual 25mm screwed conduit entries top and bottom allows four ways to surface wire the switch
- Fixed earth and neutral connector bars with dual clamping screws per tunnel provide equal stripping lengths and secure clamping for all cables
- IP66 certified



Part-Time Protection

Will your visitors get a shocking welcome?

Is he about to turn on the tears?

Are you sure your socket cover is providing you with safety protection AT ALL TIMES?

Can lightning strike in a sunny outdoor environment through an unprotected outdoor socket?

Could your air conditioner permanently chill you if you attempt maintenance in the rain?

About Schneider Electric

As a global specialist in energy management with operations in more than 100 countries, Schneider Electric offers integrated solutions across multiple market segments, including leadership positions in Utilities & Infrastructures, Industries & Machine Manufacturers, Non-residential Buildings, Data Centres & Networks and in Residential. Focused on making energy safe, reliable, efficient, productive and green, the Group's 130,000 plus employees achieved sales of 22.4 billion euros in 2011, through an active commitment to help individuals and organizations make the most of their energy.

The LifeSpace Business of Schneider Electric provides solutions that represent the best in lifestyle and innovation for offices, hotels and homes. These solutions include award-winning products in the areas of building and home automation, structured cabling, and designer switches and sockets. They help the finest architectures around the world to achieve more with less.

www.schneider-electric.com

Kavacha

You need Full-Time Protection!

Conventional weatherproof covers help to keep switches and sockets dry when they are closed, but they must be opened for people to use the switches and sockets. This creates the strange scenario where the protection is gone when you need it most.



Schneider
Electric

All rights reserved by Schneider Electric.
SE022-0511-00

With its patent-pending design, Kavacha **Full-Time** weatherproof covers enable the switches and sockets to be operative even when the covers are closed, offering uninterrupted protection. You and your family get **Full-Time Protection** if someone touches the area with wet hands, and in a humid environment. Kavacha is the ideal domestic Full-Time Weatherproof and Waterproof Solution developed specially to offer full-time protection in areas around the home that are specially susceptible to water, rain and moisture.

Full-time protection

Schneider Electric



Full-Time Protection

Welcome your visitors safely with the easily-installed **Kavacha Weatherproof Door Bell**

Keep everyone smiling with extra-safe switches protected by the totally **Kavacha Full-Time Weatherproof Membrane Switch Cover**

Get high quality weatherproof electrical socket outlet protection at all times with the **Kavacha Full-Time Weatherproof Socket Cover**

Strike out the danger with **Kavacha AS** industrial strength electrical point protection for the great outdoors

Your air conditioner won't leave you cold with a professional grade **Kavacha W** isolating switch installed

Catalogue Number	Commercial Description
Kavacha Full-Time Weatherproof Cover	
E223M TR	Full-Time Weatherproof Membrane Switch Cover (Transparent) IP55
E223M WE	Full-Time Weatherproof Membrane Switch Cover (White) IP55
E223R TR	Full-Time Weatherproof Single Gang Socket Cover (Transparent) IP55
E223R WE	Full-Time Weatherproof Single Gang Socket Cover (White) IP55
ET223R TR	Full-Time Weatherproof Twin Gang Socket Cover (Transparent) IP55
ET223R WE	Full-Time Weatherproof Twin Gang Socket Cover (White) IP55



Kavacha Weatherproof Door Bell	
A3031WBPYG	Weatherproof Surface Mount Door Bell with LED Indicator (Grey) IP44
A3031WBPWE	Weatherproof Surface Mount Door Bell with LED Indicator (White) IP44



A3031WBPYG A3031WBPWE

Kavacha AS	
CSC313	13A 250V Surface Mount Single Pole Switched Socket IP56
CSC315RP	15A 250V Surface Mount Single Pole Switched Socket IP56
CSC316RP	16A 250V Surface Mount Single Pole Switched Socket IP56
CSC316RPD	16A 250V Surface Mount Double Pole Switched Socket IP56
CSC313N	13A 250V Surface Mount Single Pole Switched Socket with Neon IP56
CSC315RPN	15A 250V Surface Mount Single Pole Switched Socket with Neon IP56
CSC316RPN	16A 250V Surface Mount Single Pole Switched Socket with Neon IP56
CSC316RPDN	16A 250V Surface Mount Double Pole Switched Socket with Neon IP56
CSO313	13A 250V Surface Mount Single Gang Socket Outlet IP56
CSO315RP	15A 250V Surface Mount Single Gang Socket Outlet IP56
CSO316RP	16A 250V Surface Mount Single Gang Socket Outlet IP56
CSO313/2	13A 250V Surface Mount Twin Gang Socket Outlet IP56
CSS116	16A 250V Surface Mount Single Pole Isolating Switch IP66
CSS120	20A 250V Surface Mount Single Pole Isolating Switch IP66
CSS132	32A 250V Surface Mount Single Pole Isolating Switch IP66
CSS140	40A 250V Surface Mount Single Pole Isolating Switch IP66
CSS220	20A 500V Surface Mount Double Pole Isolating Switch IP66
CSS232	32A 500V Surface Mount Double Pole Isolating Switch IP66
CSS240	40A 500V Surface Mount Double Pole Isolating Switch IP66
CSS320	20A 500V Surface Mount Triple Pole Isolating Switch IP66
CSS332	32A 500V Surface Mount Triple Pole Isolating Switch IP66
CSS340	40A 500V Surface Mount Triple Pole Isolating Switch IP66
CSS440	40A 415V Surface Mount Four Pole Isolating Switch IP66
CSS120N	20A 250V Surface Mount Single Pole Isolating Switch with Neon IP66
CSS220N	20A 500V Surface Mount Double Pole Isolating Switch with Neon IP66
CSS316N	16A 500V Surface Mount Triple Pole Isolating Switch with Neon IP66
CSS320N	20A 500V Surface Mount Triple Pole Isolating Switch with Neon IP66
CSS332N	32A 500V Surface Mount Triple Pole Isolating Switch with Neon IP66
CSS340N	40A 500V Surface Mount Triple Pole Isolating Switch with Neon IP66
CSW110	10AX 250V Surface Mount One Gang Two Way Switch IP66

Kavacha AS	
CSW110BPR	10AX 250V Surface Mount One Gang Two Way Press Return Switch IP66
CSW120	20A/16AX 250V Surface Mount One Gang Two Way Switch IP66
CSW220	20A 250V Surface Mount One Gang Double Pole Switch IP66
CSW110N	10AX 250V Surface Mount One Gang Two Way Switch with Neon IP66
CSW120N	20A/16AX 250V Surface Mount One Gang Two Way Switch with Neon IP66
CSW220N	20A 250V Surface Mount One Gang Double Pole Switch with Neon IP66
CSW110/2	10AX 250V Surface Mount Two Gang Two Way Switch IP66
CSW120/2	20A/16AX 250V Surface Mount Two Gang Two Way Switch IP66
CSW220/2	20A 250V Surface Mount Two Gang Double Pole Switch IP66
CSW110/2N	10AX 250V Surface Mount Two Gang Two Way Switch with Neon IP66
CSW120/2N	20A/16AX 250V Surface Mount Two Gang Two Way Switch with Neon IP66
CSW220/2N	20A 250V Surface Mount Two Gang Double Pole Switch with Neon IP66



Kavacha W	
WHS20	20A 250V Surface Mount Single Pole Isolating Switch IP66
WHS35	35A 250V Surface Mount Single Pole Isolating Switch IP66
WHS55	55A 250V Surface Mount Single Pole Isolating Switch IP66
WHS63	63A 250V Surface Mount Single Pole Isolating Switch IP66
WHD20	20A 440V Surface Mount Double Pole Isolating Switch IP66
WHD35	35A 440V Surface Mount Double Pole Isolating Switch IP66
WHD55	55A 440V Surface Mount Double Pole Isolating Switch IP66
WHD63	63A 440V Surface Mount Double Pole Isolating Switch IP66
WHT20	20A 440V Surface Mount Triple Pole Isolating Switch IP66
WHT35	35A 440V Surface Mount Triple Pole Isolating Switch IP66
WHT55	55A 440V Surface Mount Triple Pole Isolating Switch IP66
WHT63	63A 440V Surface Mount Triple Pole Isolating Switch IP66
WHT80	80A 440V Surface Mount Triple Pole Isolating Switch IP66

