

Galaxy VS 208 V and 480 V

To whom it may concern. This is to certify that Galaxy VS 208 V and 480 V UPS systems are manufactured in the following country(ies):

UPSs

Commercial reference	Description	Country of origin	Manufacturing facility
GVSUPS20KGS	Galaxy VS UPS 20kW 480V for External Batteries, Start-up 5x8	India	American Power Conversion Private Ltd - Bangalore
GVSUPS30KGS	Galaxy VS UPS 30kW 480V for External Batteries, Start-up 5x8		
GVSUPS40KGS	Galaxy VS UPS 40kW 480V for External Batteries, Start-up 5x8		
GVSUPS50KGS	Galaxy VS UPS 50kW 480V for External Batteries, Start-up 5x8		
GVSUPS60KGS	Galaxy VS UPS 60kW 480V for External Batteries, Start-up 5x8		
GVSUPS80KGS	Galaxy VS UPS 80kW 480V for External Batteries, Start-up 5x8		
GVSUPS100KGS	Galaxy VS UPS 100kW 480V for External Batteries, Start-up 5x8		
GVSUPS10KFS	Galaxy VS UPS 10kW 208V for External Batteries, Start-up 5x8		
GVSUPS15KFS	Galaxy VS UPS 15kW 208V for External Batteries, Start-up 5x8		
GVSUPS20KFS	Galaxy VS UPS 20kW 208V for External Batteries, Start-up 5x8		
GVSUPS25KFS	Galaxy VS UPS 25kW 208V for External Batteries, Start-up 5x8		
GVSUPS30KFS	Galaxy VS UPS 30kW 208V for External Batteries, Start-up 5x8		
GVSUPS40KFS	Galaxy VS UPS 40kW 208V for External Batteries, Start-up 5x8		
GVSUPS50KFS	Galaxy VS UPS 50kW 208V for External Batteries, Start-up 5x8		

Battery Solutions

Commercial reference	Description	Country of origin	Manufacturing facility
GVSCBT1	Galaxy VS Classic Battery Cabinet, UL, Type 1	United States	Termaco, Reading, PA
GVSCBT2	Galaxy VS Classic Battery Cabinet, UL, Type 2		
GVSCBT3	Galaxy VS Classic Battery Cabinet, UL, Type 3		
GVSCBT4	Galaxy VS Classic Battery Cabinet, UL, Type 4		

Commercial reference	Description	Country of origin	Manufacturing facility
GVSCBT5	Galaxy VS Classic Battery Cabinet, UL, Type 5	United States	Termaco, Reading, PA
GVSCBT1ST	Galaxy VS Classic Battery Cabinet, UL, Type 1, Seismic Compliant		
GVSCBT2ST	Galaxy VS Classic Battery Cabinet, UL, Type 2, Seismic Compliant		
GVSCBT3ST	Galaxy VS Classic Battery Cabinet, UL, Type 3, Seismic Compliant		
GVSCBT4ST	Galaxy VS Classic Battery Cabinet, UL, Type 4, Seismic Compliant		
GVSCBT5ST	Galaxy VS Classic Battery Cabinet, UL, Type 5, Seismic Compliant		

Maintenance Bypass Cabinets

Commercial reference	Description	Country of origin	Manufacturing facility
GVSBPUS80G	Galaxy VS Maintenance Bypass Cabinet, UL, Single-Unit 10-40kW 208V, 20-80kW 480V	India	American Power Conversion Private Ltd - Bangalore
GVSBPUS150G	Galaxy VS Maintenance Bypass Cabinet, UL, Single-Unit 50-75kW 208V, 100-150kW 480V		
GVSBPIT25	Galaxy VS Maintenance Bypass Cabinet with Input Transformer 10-25kW 480V or 600V In, 208V Out		
GVSBPIT50	Galaxy VS Maintenance Bypass Cabinet with Input Transformer 30-50kW 480V or 600V In, 208V Out		
GVSBPOT50	Galaxy VS Maintenance Bypass Cabinet with Output Transformer 20-50kW 480V In, 208V Out		
GVSBPOT100	Galaxy VS Maintenance Bypass Cabinet with Output Transformer 60-100kW 480V In, 208V Out		

Options

Commercial reference	Description	Country of origin	Manufacturing facility
GVSOPT001	Galaxy VS Air Filter Kit for 521mm wide UPS	India	American Power Conversion Private Ltd - Bangalore
GVSOPT002	Galaxy VS Seismic Kit for Modular Battery Cabinet or 521mm wide UPS		
GVSOPT003	Galaxy VS Seismic Kit for Maintenance Bypass Cabinet		
GVSOPT004	Galaxy VS Kirk Key Kit for Maintenance Bypass Cabinet		
GVSOPT005	Galaxy VS NEMA 2 holes kit		
GVSOPT006	Galaxy VS Parallel Communications Kit		
GVSOPT007	Galaxy VS Kirk Key Kit for Maintenance Bypass Cabinet with Transformer		
GVSOPT008	Galaxy VS Seismic kit for Maintenance Bypass Cabinet with Transformer		
GVSOPT011	Galaxy VS Cable Kit for 2nd Classic Battery Cabinet	United States	Termaco, Reading, PA
0J-0M-1160	Additional Temperature Sensor	Philippines	American Power Conversion Corporation (A.P.C.) B.V. - Cavite
0J-0P6506AA	Trip Board with Shunt Trip function for Cold start	India	American Power Conversion Private Ltd - Bangalore