

Aluminum Windings

kVA	Catalogue Number	Taps	Wiring Diagram	Weight (lbs)	Weight (kg)	Enclosure
-----	------------------	------	----------------	--------------	-------------	-----------

Three-Phase, 600V - 208Y/120V, 115 Degree rise

15						
30						
45	EE45T65HF	6-2.5% 2+4-	1	410	186	20D
75	EE75T65HF	6-2.5% 2+4-	1	620	282	21D
112.5	EE112T65HF	6-2.5% 2+4-	1	800	364	22D
150	EE150T65HF	6-2.5% 2+4-	1	1110	505	24D
225	EE225T65HF	6-2.5% 2+4-	1	1359	618	25D
300						
500						

Three-Phase, 600V - 208Y/120V, 80 Degree rise

15						
30						
45	EE45T65HB	6-2.5% 2+4-	1	410	186	20D
75	EE75T65HB	6-2.5% 2+4-	1	620	282	21D
112.5	EE112T65HB	6-2.5% 2+4-	1	800	364	22D
150						
225						
300						
500						

Single Phase, 600V - 120/240V, 115 Degree rise

15						
25						
37.5						
50						
75						
100						

Single Phase, 600V - 120/240V, 80 Degree rise

15						
25						
37.5						
50						
75						
100						

Copper Windings

kVA	Catalogue Number	Taps	Wiring Diagram	Weight (lbs)	Weight (kg)	Enclosure
-----	------------------	------	----------------	--------------	-------------	-----------

Three-Phase, 600V - 208Y/120V, 115 Degree rise

15	EE15T65HFCU	6-2.5% 2+4-	1	340	155	17D
30	EE30T65HFCU	6-2.5% 2+4-	1	372	169	18D
45						
75	EE75T65HFCU	6-2.5% 2+4-	1	725	330	21D
112.5						
150	EE150T65HFCU	6-2.5% 2+4-	1	1090	495	24D
225	EE225T65HFCU	6-2.5% 2+4-	1	1535	698	25D
300						
500						

Three-Phase, 600V - 208Y/120V, 80 Degree rise

15						
30	EE30T65HBCU	6-2.5% 2+4-	1	320	145	18D
45	EE45T65HBCU	6-2.5% 2+4-	1	410	186	20D
75	EE75T65HBCU	6-2.5% 2+4-	1	620	282	21D
112.5						
150						
225	EE225T65HBCU	6-2.5% 2+4-	1	1359	618	25D
300						
500						

Single Phase, 600V - 120/240V, 115 Degree rise

15						
25						
37.5						
50	EE50S3534HFCU	6-2.5% 2+4-	3	460	209	21D
75						
100						

Single Phase, 600V - 120/240V, 80 Degree rise

15						
25	EE25S3534HBCU	6-2.5% 2+4-	3	380	173	18H
37.5						
50						
75						
100						

- ▲ For enclosure styles, dimensions and accessories, please refer to page DE9-12.
- ■ Not for construction. Contact your local Schneider Electric sales office or your local Schneider Electric distributor.
- For detailed information please refer to catalogue "Energy Efficient Transformers" #7400CT0601.
- **These transformers do not include mechanical lug kits.** For lug kits selection information, please refer to page DE9-11 or catalog "Mechanical lug kits" #7400CT0501.
- cULus listed per CSA C22.2 No. 47, C802.2 IUL1561, NEMA ST-20, NEMA TP-2.
- For other sizes, voltages and technical data, please contact your local Schneider Electric sales office or your local Schneider Electric distributor or visit www.schneider-electric.ca.
- For transformers below 15 kVA, please refer to page DE9-6, DE9-7.

UNIQUEMENT les transformateurs triphasés et remplacés par les transformateurs EXN

