



APC Back-UPS Pro

Premium battery backup and surge protection
for your critical devices

The new APC Back-UPS Pro models provide premium battery backup and surge protection. Ideal for small or home office electronics, networking devices, gaming PCs and consoles. APC Back-UPS Pro models provide sine wave output, USB charging ports for your mobile devices, and increased runtime for your critical electronics.



www.apc.com

Life Is 

APC[®]
by Schneider Electric

APC Back-UPS Pro

Power and protect critical electronics and stay connected to the internet during outages, surges, and lightning



Sinewave power output

For advanced workstations, high end PCs, Smart TVs, multimedia devices, and home storage

2 USB charging ports (Type C+ Type A)

To maximize charging speeds and simultaneously charge mobile devices such as smartphones and tablets

Active PFC compatibility

For contemporary high end PCs and gaming users

User replaceable batteries

Allows you to quickly replace batteries

6 Battery backup outlets

Keep more devices running when the power is outside of safe levels

LCD Display

Quick and easy to read, provides information about the utility and UPS conditions

1 Gb network and coax protection

Safeguards your equipment and valuable files from “back door” surges traveling along data lines without sacrificing internet speed

Powerchute personal edition

Easy-to-use auto-shutdown software with power and energy management features

Ideal for high performance devices such as:



COMPUTER



GAMING
CONSOLE




MODEM/ROUTER/WIFI



PHONE
SYSTEMS/VOIP



WORKSTATION



TV
LCD/LED/PLASMA

USB charging ports for your mobile devices such as:



SMARTPHONE



TABLET

Life Is On

APC
by Schneider Electric



How much runtime will the Back-UPS Pro provide?

| Connected devices | Watt load | BR1000MS | BR1350MS | BR1500MS |
|--|-----------|------------|-------------|-------------|
| Entry-level desktop with 20" monitor + internet modem and router | 40 watts | 92 minutes | 110 minutes | 150 minutes |
| Notebook computer + network gateway + internet modem and router | 79 watts | 53 minutes | 66 minutes | 94 minutes |
| Mid-range PC with 20" LCD + notebook + network gateway + internet modem and router | 119 watts | 36 minutes | 46 minutes | 66 minutes |
| Gaming PC with 24" LCD monitor + external powered speakers + internet modem and router | 240 watts | 16 minutes | 22 minutes | 32 minutes |
| 42" LCD television + game console system (Xbox or PlayStation) | 335 watts | 10 minutes | 14 minutes | 21 minutes |

*Runtime and USB power will vary according to device(s), usage, and power settings.

Life Is On

APC
by Schneider Electric

APC Back-UPS Pro technical specifications

| Products specification | BR1000MS | BR1350MS | BR1500MS |
|---|--|---------------|---------------|
| Output | | | |
| Output Capacity | 1000VA / 600W | 1350VA / 810W | 1500VA / 900W |
| Output Voltage / Frequency (On utility) | 98 to 139Vac, 60Hz +/- 1Hz | | |
| Output Voltage / Frequency (On battery) | 115 Vac +/- 8%, 60Hz +/- 1Hz | | |
| Output Connections | 10 total NEMA5-15R outlets: 6 battery backup & surge and 5 surge only | | |
| Waveform Type | Sine Wave | | |
| Input | | | |
| Input Voltage / Frequency | 120 Vac, 60Hz ± 3Hz | | |
| Input Connection | Straight plug end with NEMA 5-15 | | |
| Input Cord | 6 ft cord | | |
| Surge Protection | | | |
| Surge Energy Rating | 1080 Joules | | |
| Data Line Surge Protection | 1GB dataline protection: 1-in, 1 out Network line – 10/1000BT, coaxial | | |
| Physical | | | |
| Unit Dimensions (H x W x D) | 10.47 x 3.9 x 14.5 in. | | |
| Unit Weight | 22.48 lbs. | 22.48 lbs. | 27.55 lbs. |
| Shipping Dimensions (H x W x D) | 14.11 x 5.59 x 17.40 in. | | |
| Shipping Weight | 16.75 lbs. | 17.63 lbs. | 26.23 lbs. |
| Color | Black | | |
| Battery | | | |
| Battery Type | Sealed, lead-acid, maintenance-free | | |
| Replacement Battery | APCRBC160 | APCRBC161 | APCRBC163 |
| Management | | | |
| Alarms | Visual (LCD display) and audible alarms | | |
| Shutdown S/W | PowerChute Personal Edition (via USB interface) | | |
| Warranty | | | |
| Standard Warranty Length | 3 years | | |
| Equipment Protection Policy | \$250,000 | \$500,000 | |
| Certification/Approvals | | | |
| TUV C-US certified, ENERGY STAR™, CEC, DOE, NOM | | | |

132 Fairgrounds Road
West Kingston, RI 02892
United States
Phone: +1 800-800-4272
www.apc.com

Life Is On

