


Enclosures and mini enclosures for modular switchgear

Mini enclosures



Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
1 row					
3 modules (150 x 80 x 98 mm)		13975	13956	10311	-
4 modules (200 x 123 x 112 mm)		13976	13957	10312	13441
6 modules (200 x 159 x 112 mm)		13977	13958	10313	13442
8 modules (200 x 195 x 112 mm)		13978	13959	10314	13443
12 modules (200 x 267 x 112 mm)		13979	13960	10315	13444

(1) accessories also delivered: 1 marking kit, class II plugs.

Enclosures




Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
1 row					
12 modules (280 x 340 x 160 mm)	1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 8 holes)	13981	13962	10340	13431
18 modules (280 x 448 x 160 mm)	1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 16 holes)	13982	13963	10341	13432
2 rows					
24 modules (460 x 340 x 160 mm)	1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 22 holes)	13983	13964	10342	13433
36 modules (460 x 448 x 160 mm)	1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 32 holes)	13984	13965	10343	13434
3 rows					
36 modules (610 x 340 x 160 mm)	1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 32 holes)	13985	13966	10344	13435
54 modules (610 x 448 x 160 mm)	2 terminal blocks support, 3 terminal blocks (1 x 4 holes, 2 x 22 holes)	13986	13967	10345	13436
4 rows					
72 modules (842 x 448 x 160 mm)	2 terminal blocks support, 3 terminal blocks (1 x 4 holes, 2 x 32 holes)	13987	13968	10346	13437

(1) accessories also delivered: 1 marking kit per row, 1 wiring strap per row, class II plugs and blanking plates (5 x 18 mm modules per row).

Enclosures for modular switchgear with interface

Enclosures (90 x 100 mm openings)




Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
1 row + 1 opening					
12 modules (280 x 448 x 160 mm)	1 wiring strap 1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 16 holes) 1 plate for indicator light buttons (13138)	13990	13970	10350	13438
2 rows + 3 openings					
24 modules (460 x 448 x 160 mm)	2 wiring straps 1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 22 holes) 3 plates for indicator light buttons (13138) 1 plate for 65 x 85 mm power outlet (13136)	13991	13971	10351	13439
3 rows + 4 openings					
36 modules (610 x 448 x 160 mm)	3 wiring straps 1 terminal block support, 2 terminal blocks (1 x 4 holes, 1 x 32 holes) 4 plates for indicator light buttons (13138) 1 plate for 65 x 85 mm power outlet (13136)	13992	13972	10352	13440

(1) accessories also delivered: 1 marking kit per row, class II plugs and blanking plates (5 x 18 mm modules per row).

Interface enclosures

Enclosures (65 x 100 mm openings)




Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
3 openings					
460 x 138 x 160 mm	3 plates for indicator light buttons (13138) 1 plate for 65 x 85 mm power outlet (13136)	13993	13973	10353	-
4 openings					
610 x 138 x 160 mm	4 plates for indicator light buttons (13138) 1 plate for 65 x 85 mm power outlet (13136)	13994	13974	10354	-

(1) accessories also delivered: class II plugs.

Enclosures for power outlets


Mini enclosures for power outlets (65 x 85 mm openings)



Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
1 opening					
4 modules (248 x 98 x 98,5 mm)		13175	13150	13360	-
2 openings					
4 modules (310 x 98 x 98,5 mm)	1 plate, catalogue number 13135	13176	13151	13361	-
3 openings					
4 modules (392 x 98 x 98,5 mm)	1 plate, catalogue number 13135	13177	13152	13362	-

(1) accessories also delivered: class II plug.

Enclosures for power outlets (90 x 100 mm openings)



Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
2 openings					
5 modules (460 x 138 x 160 mm)	2 plates, catalogue number 13136, 1 plate, catalogue number 13138	13178	13153	10363	-
4 openings					
8 modules (460 x 236 x 160 mm)	2 wiring straps 4 plates, catalogue number 13136, 1 plate, catalogue number 13138	13179	13154	10364	-
3 openings					
12 + 1 modules (335 x 340 x 160 mm)	2 wiring straps 3 plates, catalogue number 13136, 1 plate, catalogue number 13138	13180	13155	10365	-
6 openings					
12 + 1 modules (460 x 340 x 160 mm)	2 wiring straps 6 plates, catalogue number 13136, 2 plates, catalogue number 13138	13181	13156	10366	-
8 openings					
18 + 1 modules (460 x 448 x 160 mm)	2 wiring straps 8 plates, catalogue number 13136, 2 plates, catalogue number 13138	13182	13157	10367	-

(1) accessories also delivered: class II plugs, blanking plates (5 x 18 mm modules) and marking kit.

Enclosures for interlocked power outlets (103 x 225 mm openings)




Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
1 opening					
5 modules (460 x 138 x 160 mm)		13185	13160	10370	-
2 openings					
8 modules (460 x 236 x 160 mm)	2 wiring straps, 1 plate, catalogue number 13143	13186	13161	10371	-
3 openings					
12 + 1 modules (460 x 340 x 160 mm)	2 wiring straps, 1 plate, catalogue number 13143	13187	13162	10372	-
4 openings					
18 + 1 modules (460 x 448 x 160 mm)	2 wiring straps, 1 plate, catalogue number 13143	13188	13163	10373	-

(1) accessories also delivered: class II plugs, blanking plates (5 x 18 mm modules) and marking kit.

Versatile enclosures


Versatile enclosures with opaque door



Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
460 x 340 x 160 mm		13195	13170	10380	-
610 x 340 x 160 mm		13196	13171	10381	-
460 x 448 x 160 mm		13197	13172	10382	-
610 x 448 x 160 mm		13198	13173	10383	-
842 x 448 x 160 mm		13199	13174	10384	-

(1) accessories also delivered: class II plugs, slotted mounting plate.

Versatile enclosures for power outlets




















Accessories delivered ⁽¹⁾		Offer A	Offer B	Offer C	Offer D
5 modules (460 x 138 x 160 mm)		13189	13164	10374	-
8 modules (460 x 236 x 160 mm)		13190	13165	10375	-
12 + 1 modules (335 x 340 x 160 mm)		13191	13166	10376	-
12 + 1 modules (460 x 340 x 160 mm)		13192	13167	10377	-
18 + 1 modules (460 x 448 x 160 mm)		13193	13168	10378	-

(1) accessories also delivered: class II plugs, blanking plates (5 x 18 mm modules) and marking kit.


Kaedra

Accessories for weatherproof enclosures and mini enclosures


For implementation of enclosures		
Association kit		
	2 sleeves + 4 nuts + 4 joints	13934
Wall mounting lugs		
	wall mounting lugs (set of 4)	13935
Row separator		
	12 modules wide	13936
	18 modules wide	13937
Jack-up block		
	jack-up block	13938
Junction for trunking		
	junction for trunking	enclosure 340 mm wide
		enclosure 448 mm wide
		13939
		13929
Blanking plate		
	blanking plate (set of 10 x 5 modules)	13940
For implementation of switchgear		
Plate for 65 x 85 mm slot		
	for 50 x 50 mm power outlets	13135
Plate for 90 x 100 mm slot		
	adaptation for 65 x 85 mm power outlet base	13136
	blanking or adaptation for 65 x 65 mm or 75 x 75 mm power outlet base (screwed-on plate)	13137
	blanking or adaptation for 16 and 22 mm diameter pushbutton controls (clipped-on plate)	13138
	blanking and identification	13141
Kit for 90 x 100 mm slot		
	INS40/63/80 A	13139
	residual current circuit-breakers and other modular devices (max. 4 modules)	13140
Plate for 103 x 225 mm slot		
	adaptation (one 85 x 65 mm slot + one 90 x 100 mm slot)	13142
	blanking or adaptation for 65 x 65 mm or 75 x 75 mm power outlet base	13143
	adaptation for 63 A LV power outlet (100 x 107 mm)	13144
Plain front plate		
	12 modules	13944
	18 modules	13945
Slotted mounting plate		
	150 x 250 mm	13941

For electrical connection





Terminal block support for mini enclosure

	4 modules	13361
	6 modules	13362
	8 modules	13363
	12 modules	13364

Terminal block support for enclosure

	on chassis	12 modules	13599
		18 modules	13595


Terminal blocks kit

	5 x 4 holes (2 blue, 3 black) 2 black covers 2 green covers	13445
	1 x 8 holes (blue) 1 green cover 1 support for 8 back mounting	13446
	1 x 8 holes (blue) 1 green cover 1 support for 12 back mounting	13448
	1 x 32 holes (blue) 1 green cover 1 support for 18 back mounting	13450

Cable support sleeves

	bag of varied diameter	14190
---	------------------------	-------

Cable gland

	PG11	83992
	PG13,5	83993
	PG16	83994
	PG21	83995
	PG29	83996
	PG36	83997

Wiring strap

	wiring strap (set of 5)	13946
---	-------------------------	-------

For marking

Self-adhesive symbols

	standard	13735
	special	13736

Self-adhesive sheets

	self-adhesive sheets for SISmarker printing	13260
---	---	-------

For enclosure protection

Sealing kit

	sealing kit (2 screws, 5 fasteners)	13947
---	-------------------------------------	-------

Keylock

	keylock (Euro Locks no. 850)	13948
---	------------------------------	-------

Insert

	triangle	13949
	square	13950