



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range of product	VarSet
Device short name	Varset Classic
Device presentation	Cubicle A3
Network frequency	50 Hz
Capacitor technology	3P capacitor
Reactive power rating	570 kvar for 400 V AC 50 Hz
Number of steps	19 x 30 kvar
Network rated voltage	400...415 V AC 50 Hz
Network pollution level	No polluted (< 15 %) at 400...415 V
[Ui] rated insulation voltage	690 V

Complementary

Device composition	Circuit-breaker equipment protection Contactor Controller equipment regulation Incoming circuit-breaker equipment protection Varplus ² capacitors
Device wiring	Cables
Internal voltage transformer	400/230 V
Capacitor voltage	415 V AC 50 Hz
Capacitance tolerance	- 5 % to 10 %
Rated short-duration power frequency withstand voltage	2.5 kV 50 Hz 1 minute
Maximum permissible voltage	1.1 x Un 8 hours over 24 hours conforming to IEC 60831
[Imp] maximum permanent current	400 V : 1.3 x I1
Colour code	(RAL 9001)
Height	2000 mm
Width	800 mm
Depth	600 mm
Product weight	215 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN 60439-1 IEC 60439-1 IEC 61921
IP degree of protection	IP31
Ambient air temperature for operation	-5...40 °C
Average ambient air temperature for operation	25 °C (annual) 35 °C (over 24 hours)

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**

52954 may be replaced by any of the following products:



VLVAF5N03522AA

VarSet capacitor bank Auto 600kvar with incomer CB xxB 400V 50Hz

Qty 1

Reason for Substitution: End of life | Substitution date: 04 Jan 2013 | Mixage pièces ancienne / nouvelle gamme incompatible.



VLVAF5N03522AA

VarSet capacitor bank Auto 600kvar with incomer CB xxB 400V 50Hz

Qty 1

Reason for Substitution: End of life | Substitution date: 04 Jan 2013 | Mixage pièces ancienne / nouvelle gamme incompatible.