

# Product data sheet

## Characteristics

# 8501KP13P14V14

Plug-In Relay - 11 pin plug-in - 3 poles - 24VAC coil - pilot light



by Schneider Electric



Product availability: Stock - Normally stocked in distribution facility

Price\*: 64.66 USD



### Main

|                              |                                      |
|------------------------------|--------------------------------------|
| Range of product             | 8501K                                |
| Product or component type    | Relay                                |
| Relay type                   | General purpose                      |
| Mounting support             | Socket                               |
| Switch function              | 3PDT                                 |
| [Uc] control circuit voltage | 24 V AC                              |
| Local signalling             | Indicator light when relay energised |
| Control type                 | Without test button                  |

### Complementary

|                           |  |
|---------------------------|--|
| Rated power in hp         | 0.33 hp at 120 V<br>0.5 hp at 240 V  |
| Rated breaking capacity   | 3 A at 120 V AC - inductive control circuit per UL 508<br>1.5 A at 240 V AC - inductive control circuit per UL 508<br>10 A at 28 V DC - resistive control circuit per UL 508<br>10 A at 120 V AC - resistive control circuit per UL 508<br>6.66 A at 240 V AC - resistive control circuit per UL 508 |
| Maximum switching voltage | 300 V at AC<br>30 V at DC  |
| Contacts material         | Silver tin oxide   |
| Operating time            | 12 ms - pick-up<br>12 ms - drop-out  |
| Shape of pin              | Tubular  |
| Product compatibility     | 8501NR62<br>8501NR61   |


## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -40...113 °F                                    |
| Product certifications                | RoHS<br>CSA<br>CE<br>UL listed<br>UL recognized |
| Height                                | 2.66 in   |
| Width                                 | 1.39 in   |
| Depth                                 | 1.39 in   |

## Ordering and shipping details

|                       |                     |
|-----------------------|---------------------|
| Category              | 21141 - 8501 KP     |
| Discount Schedule     | CP2                 |
| GTIN                  | 00785901490647      |
| Nbr. of units in pkg. | 1                   |
| Package weight(Lbs)   | 0.20000000000000001 |
| Returnability         | N                   |
| Country of origin     | CN                  |

## Offer Sustainability

|                                  |  |
|----------------------------------|--|
| Sustainable offer status         | Green Premium product  |
| RoHS (date code: YYWW)           | Compliant - since 1430 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold  |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |
| California proposition 65        | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1                | Nickel compounds, which is known to the State of California to cause cancer, and   |
| ----- Substance 2                | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.   |
| ----- More information           | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>  |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **Commercialised**

## 8501KP13P14V14 may be replaced by any of the following products:



### 8501KPR13P14V14

Plug in relay, 11 pin, 3PDT, 10 amp at 277 VAC, 24 VAC coil, pilot light

Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2017 | Replacement product Has a UL rating of 10A



### 8501KPR13P14V14

Plug in relay, 11 pin, 3PDT, 10 amp at 277 VAC, 24 VAC coil, pilot light

Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2017 | Replacement product Has a UL rating of 10A