

# Product data sheet

## Characteristics

# 8501KUD13V53

Plug-In Relay - 11 blade plug-in - 3 poles - 24VDC coil



by Schneider Electric

Price\*: 30.01 USD



### Commercial status

This Product is Obsolete :

**⚠ This Product is Obsolete**

### Main

Range of product	8501K
Product or component type	Relay
Relay type	General purpose
Mounting support	Socket
Switch function	3PDT
[Uc] control circuit voltage	24 V DC
Local signalling	No indicator
Control type	Without test button

### Complementary

Rated power in hp	0.33 hp at 120 V 0.5 hp at 240 V
Rated breaking capacity	3 A at 120 V AC - inductive control circuit per UL 508 1.5 A at 240 V AC - inductive control circuit per UL 508 10 A at 28 V DC - resistive control circuit per UL 508 10 A at 120 V AC - resistive control circuit per UL 508 6.66 A at 240 V AC - resistive control circuit per UL 508
Maximum switching voltage	300 V at AC 30 V at DC
Contacts material	Silver tin oxide
Operating time	11 ms - pick-up 7 ms - drop-out
Shape of pin	Spade
Product compatibility	8501NR82


## Environment

Ambient air temperature for operation	-40...158 °F
Product certifications	CE UL recognized RoHS UL listed CSA
Height	2.07 in
Width	1.52 in
Depth	1.42 in

## Ordering and shipping details

Category	21144 - 8501 KU
Discount Schedule	CP2
GTIN	00785901480778
Nbr. of units in pkg.	1
Package weight(Lbs)	0.19
Returnability	Y
Country of origin	CN

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**

8501KUD13V53 may be replaced by any of the following products:



### 8501KUDR13V53

Plug in relay, 11 blade, 3PDT, 10 amp at 277 VAC, 24 VDC coil

Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2017 | Replacement product Has a UL rating of 10A



### 8501KUDR13V53

Plug in relay, 11 blade, 3PDT, 10 amp at 277 VAC, 24 VDC coil

Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2017 | Replacement product Has a UL rating of 10A