Product data sheet
Characteristics

MA9IMA12
Surge protection module, Surgelogic, MA, 120kA, 600 VAC delta, 3 phase, 3 wire, SPD type 2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 600.00 USD

Main

Product or Component Type	Surge protection module
Range of Product	Surgelogic
Device short name	IMA
Accessory / separate part category	Replacement part

Complementary

[Ue] rated operational voltage	600 V delta AC
[Uc] maximum continuous operating voltage	700 V
Short-circuit protection	200 KA
Surge current	120 KA
Nominal Discharge Current	20 KA
Phase	3 phase
Wiring configuration	3-wire
Connections - terminals	Terminals
Local signalling	Status LED green normal operation
Provided equipment	Alarm enable/disable switch
Mounting Support	Panel mounting
Height	6.25 In (158.8 mm)
Width	3.26 In (82.8 mm)
Depth	2.69 In (68.3 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Environment

Ambient Air Temperature for Operation	149 °F (65 °C)
NEMA Degree of Protection	NEMA 2
Enclosure material	Black Plastic
Standards	UL 1449:ed. 4 UL 1283:ed. 5 CSA C22.2 No 8:1986 ANSI/IEEE C62.41 ANSI/IEEE C62.45 NEC 285

Ordering and shipping details

Category	US1DE1B08467
Discount Schedule	DE1B
GTIN	3606486148365
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.26 In (15.9 cm)
Package 1 Width	3.27 In (8.3 cm)
Package 1 Length	2.68 In (6.8 cm)
Package 1 Weight	2.44 Lb(US) (1.107 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised