

# Product data sheet

## Characteristics

# LAP36350MB

## FA/LA MOLDED CASE CIRCUIT BREAKER, 600V, 350A, 3P, I-Line, SHORT HANDLE



by Schneider Electric



Product availability: Stock - Normally stocked in distribution facility

Price\*: 4619.00 USD

### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Magnetic
Breaking capacity code	A
Accessory / separate part type	Handle

### Complementary

Line Rated Current	350 A
Poles description	3P
Breaking capacity	42 KA 120 V AC 42 KA 240 V AC 30 KA 480Y/277 V AC 30 KA 480 V AC 22 KA 600 V AC
[Ue] rated operational voltage	600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load Terminal line
AWG gauge	AWG 1...600 kcmil aluminium/copper)1 AWG 1...250 kcmil aluminium/copper)2
Terminal identifier	AL400LA
Magnetic hold current	1750 A
Magnetic tripping current	3500 A
Operator profile	Short lever
Wiring configuration	3-wire
Maximum Height	11 ln (279.40 mm)
Width	6 ln (152.40 mm)
Depth	5.84 ln (148.34 mm)

### Environment

Product certifications	UL Listed CSA IEC
------------------------	-------------------------

### Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901530084
Package weight(Lbs)	15.8 Lb(US) (7.17 kg)
Returnability	Yes
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP and DIDP- which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**