

# Product data sheet

## Characteristics

# VW3L2M211R100

pre-assembled cable kit - 2 I/O, 1 STO insert for motion sequence - 10 m



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1009.08 USD



### Main

|                                       |  |
|---------------------------------------|--|
| Product or component type             | Pre-assembled cable kits for motion sequence with 2 I/O, 1 STO insert  |
| Accessory / separate part type        | Cable  |
| Accessory / separate part category    | Connection accessories   |
| Accessory / separate part destination | For drives with printed circuit board connectors   |
| Cable length                          | 32.81 Ft (10 m)  |
| Additional information                | With integrated cable entry with strain relief<br>With insert equipped with 2 I/O and 1 safe torque off via M8 connector |

### Complementary

|                         |   |
|-------------------------|---|
| Range compatibility     | Lexium ILE<br>Lexium ILA<br>Lexium ILS                  |
| Communication interface | I/O for motion sequence                                 |
| Electrical connection   | Printed circuit board connector drive<br>Cable end open |
| Net weight              | 3.31 Lb(US) (1.5 kg)                                    |

### Ordering and shipping details

|                       |                                      |
|-----------------------|--------------------------------------|
| Category              | 18289 - LEXIUM INTEGRATED DRIVES ACC |
| Discount Schedule     | PC56                                 |
| GTIN                  | 03389118367425                       |
| Nbr. of units in pkg. | 1                                    |
| Package weight(Lbs)   | 3.3 Lb(US) (1.50 kg)                 |
| Returnability         | No                                   |
| Country of origin     | DE                                   |

## Packing Units

|                        |                  |
|------------------------|------------------|
| Unit Type of Package 1 | PCE              |
| Package 1 Height       | 3.94 In (10 cm)  |
| Package 1 width        | 11.81 In (30 cm) |
| Package 1 Length       | 11.81 In (30 cm) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive-harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End Of Life Information</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**