

# Back-UPS™ SX3 650

Part Number: SX3650CI-FR



## Battery Backup with Surge Protection for Electronics and Computers

The Back-UPS SX3 650 by Schneider Electric protects your electronic equipment from damage due to power outages, surges and spikes while providing short term battery power during an outage. The Back-UPS SX3 650 features Automatic Voltage Regulation (AVR), which instantly adjusts high and low voltages to safe levels for your electronics, so you can work indefinitely through sustained fluctuations. Specifically designed to protect your equipment and network connection in harsh power environments, the Back-UPS SX3 650 ensures maximum productivity and work efficiency.

### Product Applications:

- PC and peripherals
- Networking equipment (router, modem)
- Network Attached Storage (NAS)
- Projectors with impulse power



### Product Features:

- 1 LED Indicator and Audible Alarms**  
Quickly understand the unit and power status through visual and audible indicators.
- 2 Automatic Voltage Regulation (AVR)**  
**Input voltage range 140 – 300 V**  
AVR instantly corrects voltage fluctuations without using the battery, allowing you to work indefinitely through sustained voltage increases and decreases.
- 3 Battery Backup and Surge Protected Outlets**  
Keep critical electronic equipment running when the power goes out or fluctuates at dangerous levels, so you can protect your work and save your data.
- 4 Push Button Circuit Breaker**  
Provides for easy recovery from circuit overloads and protects your fuse box and electronics from electrical damage.
- 5 Automatic Diagnostic Testing**  
Periodic battery self-test provides early detection of a battery that needs to be replaced, ensuring your unit is ready when you need it.
- 6 2 Yr Warranty**  
Schneider Electric offers a 2 year warranty with free technical phone and online support, providing customer peace of mind.
- 7 Easy to use “one step” battery connector.**

## Back-UPS SX3650CI-FR Specifications

Model Number	SX3650CI-FR
<b>Output</b>	
Output Capacity	650 VA / 390 Watts
Output Voltage / Frequency (On utility)	230V / 50/60Hz +/- 3 Hz
Output Voltage / Frequency (On battery)	230V +/-8%, 50 or 60 Hz +/-1Hz (auto-sensing)
Output Connections	3 French/Belgian Sockets (all with battery backup and surge protection)
Waveform Type	Stepped Approximation to Sine Wave
<b>Input</b>	
Input Voltage / Frequency	140-300 V / 45-65 Hz
Input Connection	French/Belgian
<b>Surge Protection</b>	
AC Power Surge Protection	All outlets
<b>Physical</b>	
Unit Dimensions (H x W x D)	200 x 115 x 257 mm
Unit Weight	6.2 Kg
Shipping Dimensions (H x W x D)	270 x 198 x 340 mm
Shipping Weight	7.0 Kg
Color	Black
UPC Code	731304307846
<b>Battery</b>	
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte; leak proof
Battery Size	12 volt, 7.2 Ah
<b>Management</b>	
Alarms	Visual (LED) and audible alarms
Adjustable Sensitivity and Transfer Voltage	Low, Medium (default), High

**APC by Schneider Electric**

132 Fairgrounds Rd  
West Kingston, RI 02892

[www.apc.com](http://www.apc.com)

