

Product data sheet

Characteristics

QO12040M200RB

Load center, QO, 1 phase, 20 spaces, 40 circuits, 200A convertible main breaker, NEMA3R, UL



Product availability: Stock - Normally stocked in distribution facility

Price*: 954.00 USD



Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Range of product	QO
Product or component type	Load Center
Enclosure type	Weatherproof enclosure
Cover type	Surface cover

Complementary

Load center type	Main breaker
Line Rated Current	200 A
Number of spaces	20
Short-circuit current	22 KA
Number of circuits	40
Number of tandem circuit breakers	20
Phase	1 phase
[Ue] rated operational voltage	120/240 V AC
AWG gauge	AWG 4...250 kcmil aluminium/copper
Electrical connection	Lugs
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel Gray
Box number	5R
Height	26.02 In (661 mm)
Maximum Width	14.76 In (375 mm)

Environment

NEMA degree of protection	NEMA 3R outdoor
Ambient air temperature for operation	23 °F (-5 °C) 104 °F (40 °C)
Product certifications	UL Listed

Ordering and shipping details

Category	00002 - QO 1PH LC,12-42 CKT,NEMA3R
Discount Schedule	DE3A
GTIN	00785901867975
Nbr. of units in pkg.	1
Package weight(Lbs)	30.08 Lb(US) (13.64 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	27.60 In (70.104 cm)
Package 1 width	5.20 In (13.208 cm)
Package 1 Length	15.50 In (39.370 cm)

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**

QO12040M200RB may be replaced by any of the following products:



QO120M200PRB

Load center, QO, 1 phase, 20 spaces, 20 circuits, 200A convertible main breaker, PoN, NEMA3R, UL

Qty 1

Reason for Substitution: End of life | Substitution date: 04 Mar 2020 |



QO120M200PRB

Load center, QO, 1 phase, 20 spaces, 20 circuits, 200A convertible main breaker, PoN, NEMA3R, UL

Qty 1

Reason for Substitution: End of life | Substitution date: 04 Mar 2020 |