

Back-UPS™ SX3 800 / 1100

Part Number: SX3800CI-FR, SX31100CI-FR



Battery Backup with Surge Protection for Electronics and Computers

Schneider Electric's Back-UPS SX3 800 and 1100 protect your electronic equipment from damage due to power outages, surges, and spikes while providing short term battery power during an outage. Back-UPS SX3 800 and 1100 both feature Automatic Voltage Regulation (AVR), which instantly adjusts high and low voltages to a safe level for your electronics, so you can work indefinitely through sustained fluctuations. Specifically designed to protect your equipment and network connection in harsh power environments, the Back-UPS SX3 800 and 1100 ensure maximum productivity and work efficiency.

Product Applications:

- PC and peripherals
- Networking equipment (router, modem)
- Game Consoles
- LCD / LED TV
- Projectors with impulse power



Product Features:

- 1 Power Button / LED Indicator and Audible Alarms**
Quickly understand the unit and power status through visual and audible indicators.
- 2 Automatic Voltage Regulation (AVR)**
Input voltage range 150 – 280 V
AVR instantly corrects voltage fluctuations without using the battery, allowing you to work indefinitely through sustained voltage increases and decreases.
- 3 4 Battery Backup & Surge Protected Sockets**
Keep critical electronic equipment running when the power goes out or fluctuates at dangerous levels, so you can protect your work and save your data.
- 4 Push Button Circuit Breaker**
Provides for easy recovery from circuit overloads and protects your fuse box and electronics from electrical damage.
- 5 Automatic Diagnostic Testing**
Periodic battery self-test provides early detection of a battery that needs to be replaced, ensuring your unit is ready when you need it.
- 6 2 Yr Warranty**
Schneider Electric offers a 2 year warranty with free technical phone and online support, providing customer peace of mind.
- 7 Easy to use “one step” battery connector.**

Back-UPS SX3800CI / SX31K1CI Specifications

Model Number	SX3800CI-FR	SX31K1CI-FR
Output		
Output Capacity	800 VA / 480 Watts	1100 VA / 660 Watts
Output Voltage / Frequency (On utility)	230V / 50/60+/-3 Hz	
Output Voltage / Frequency (On battery)	230V +/-8%, 50 or 60 Hz +/-1 Hz (auto-sensing)	
Output Connections	(4) French/Belgian Sockets (all with battery backup and surge protection)	
Waveform Type	Stepped Approximation to Sine Wave	
Input		
Input Voltage / Frequency	150 – 280 V / 50/60Hz +/-3 Hz (default:50Hz)	
Input Connection	French/Belgian	
Surge Protection		
AC Power Surge Protection	All sockets	
Physical		
Unit Dimensions (H x W x D)	215 x 130 x 336 mm	
Unit Weight	8.0 Kg	12.0 Kg
Shipping Dimensions (H x W x D)	295 x 245 x 440 mm	
Shipping Weight	8.79 Kg	12.92 Kg
Color	Black	
UPC Code	731304314295	731304314288
Battery		
Battery Type	Maintenance-free, sealed lead-acid battery, leak proof	
Battery Size	12 volt, 9.0 Ah	12 volt, 7.2 Ah x 2
Management		
Alarms	Visual (LED) and audible alarms	
Adjustable Sensitivity and Transfer Voltage	Low, Medium (default), High	

APC by Schneider Electric

132 Fairgrounds Rd
West Kingston, RI 02892

www.apc.com

