



ARGUS Presence detector Dual-Tech with PIR and Ultrasonic detection - 1 channel



Version	Art. no.
	CCT551011

Presence detector for ceiling mounting. Integrating PIR and Ultrasonic (US) technology, this device is a sophisticated motion detector, offering a highly effective solution for a wide variety of applications. These sensors detect occupancy by monitoring frequency shifts caused by minor movements such as typing or reading, but with the added benefit of preventing false triggering. Ideal for use in public conveniences, underground car parks, libraries, open plan offices and classrooms.

Functions:

- Detection mode options: PIR + US, PIR only, US only, PIR or US
- External triggering via push-button
- Remote setting and switching
- Brightness-dependent staircase lighting function
- Suitable for flush or surface mounting

Mains voltage: AC 220–240 V, 50/60 Hz

Nominal power:

- LED lamps: 100 W
- Incandescent lamps AC 230 V: 2000 W
- Halogen lamps AC 230 V: 1000 W
- Halogen with electronic transformer: 1000 VA
- Halogen with iron core transformer: 1000 VA
- Fluorescent tubes: 900 VA
- Compact fluorescent lamps: 100 W

Upstream fuse: 10 A

Power consumption: < 2 W

Angle of detection: 360°

Range US: Area of max. 10x16 m (at 2.5 m mounting height)

Range PIR: Ø 8 m (at 2.5 m mounting height)

Light sensor (sensitivity): 10–1000 Lux

Time setting: from approx. 5 s to approx. 30 min

Switching mode: Automatic

Connection: 3-wire, neutral conductor **required**

Operating temperature: at room temperature

IP protection rating: IP20

Colour: white

Dimensions (LxWxH):

Ø112 x 90 mm (flush mounted)

Ø112 x 72 mm (surface mounted)

Accessories: IR remote control for ARGUS Presence detector Dual-Tech CCT556011

IR remote control for ARGUS Presence detector Dual-Tech



Version	Art. no.
	CCT556011

IR remote control for activating

- ARGUS Presence detector Dual-Tech with PIR and Ultrasonic detection - 1 channel
- ARGUS Presence detector Dual-Tech with PIR and Ultrasonic detection - 2 channel

Battery: CR2032

Range: up to 10 m

To be completed with: ARGUS Presence detector Dual-Tech with PIR and Ultrasonic detection - 1 channel

CCT551011

ARGUS Presence detector Dual-Tech with PIR and Ultrasonic detection - 2 channel

CCT551012



The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.