

# Product update

## New Kaedra range of enclosures for modular equipment Replacement to obsolete Mureva range

>March 2012



The Kaedra enclosures offer a complete range of multi-functional weatherproof enclosures from 5 to 72 modules which combine style and robustness. This new range of products is a replacement offer for the Mureva range of enclosures for modular equipment which is now obsolete.



Kaedra is the best solution for applications in demanding environments e.g. Final LV distribution in outdoor or severe conditions such as dust, humidity, heat, public areas. It offers a complete installation which combines 3 essential functions: distribution, power supply and electrical control. The Kaedra range really lets you save time and great flexibility.

### Existing Mureva to Kaedra features

- > Quick access to power outlets and control devices
- > Openings allow rapid installation of all devices directly or using matching plates
- > IP65, sealed tight to protect against the entry of solid or liquid materials
- > IK09 giving high impact strength and resistance to chemical and atmospheric agents, e.g. UV.
- > Class 2 insulating material
- > Optional door lock and sealing of the front face and front plates
- > Enclosure RAL 7035

### Additional Kaedra features

- > Range consisting of 5 – 72 modules (Mureva limited to 54 modules)
- > Cable inlet and internal distribution simplified
- > Conformity with IEC 670 standard for empty enclosures and with IEC 439-3 standard for equipment boards
- > New attractive colour and ergonomic design allow for more cabling space and make the Kaedra switchboards ideal for use even in places visible to the general public.
- > Transparent light green door enable immediate checking of operating conditions

### The range

- > Enclosure for modular switchgear 3 – 72 modules
- > Enclosures for modular switchgear with interface 12, 24 and 36 modules
- > Enclosures for power outlets 2 or 3 openings
- > Universal enclosures 5 sizes



SE Part No Mureva	Mureva Description Kaedra	SE Part No	Kaedra Description
ENN82050	Modular Mixed 5M	13189	enclosure 5 modular with blank area
ENN82051	Modular Mixed 8M	13190	enclosure 8 modular with blank area
ENN82052	Modular Mixed Low 13M	13191	enclosure 12 modular with blank area
ENN82053	Modular Mixed High 13M	13192	enclosure 12 modular with blank area
ENN82062	Universal enclosure 610x340	13197	Universal enclosure 448x460
ENN82063	Universal enclosure 610x450	13198	Universal enclosure 610x448x160
		13392	2 SP way Mini Opale plastic enclosure
		13394	4 SP way Mini Opale plastic enclosure
		13396	+ SP way Mini Opale plastic enclosure
		13398	8 SP way Mini Opale plastic enclosure
ENN82111	24 mod DHE Box	13433	2 row 24 modular insulated enclosure
ENN82112	IP65 36 Way Modular	13435	3 row 36 modular insulated enclosure
ENN82102	Mini Modular Box 4M E + N	13441	4 modular insulated enclosure
ENN82002	Mini Modular Box 4M	13441	4 modular insulated enclosure
ENN82103	Mini Modular Box 6M E + N	13442	6 modular insulated enclosure
ENN82003	Mini Modular Box 6M	13442	6 modular insulated enclosure
ENN82104	Mini Modular Box 8M E + N	13443	8 modular insulated enclosure
ENN82004	Mini Modular Box 8M	13443	8 modular insulated enclosure
ENN82110	Mod. Enclosure - 12	13444	12 modular insulated enclosure
ENN82105	Mini Modular Box 12M E + N	13444	12 modular insulated enclosure
ENN82005	Mini Modular Box 12M	13444	12 modular insulated enclosure
ENN82010	Modular Box 12M	13444	12 modular insulated enclosure
ENN82001	Mini Modular Box 3M	13975	3 modular insulated enclosure
ENN82101	Mini Modular Box 3M E + N	13975	3 modular insulated enclosure
ENN82201	COF.S/T MINI IP65 3 MOD.	13975	3 modular insulated enclosure
ENN82202	COF.S/T MINI IP65 4 MOD.	13976	4 modular insulated enclosure
ENN82203		13977	6 modular insulated enclosure
ENN82204		13978	8 modular insulated enclosure
ENN82205		13979	12 modular insulated enclosure
ENN82020	Modular Box 18M	13982	18 modular insulated enclosure 1 row
ENN82011	Modular Box 2x12M	13983	enclosure 2Ax12 modular
ENN82121	TIGHT MODULAR BOX DHE	13984	36 modular enclosure
ENN82021	Modular Box 2x18M	13984	36 modular enclosure
ENN82012	Modular Box 3x12M	13985	36 modular insulated enclosure 3 row
ENN82122	TIGHT MODULAR BOX DHE	13986	enclosure 3 x 18 modular
ENN82022	Modular Box 3x18M	13986	enclosure 3 x 18 modular

For more information please contact us on 0870 608 8 608  
or visit [www.schneider-electric.com/uk](http://www.schneider-electric.com/uk)