



CATALOG NUMBER	PRIMARY VOLTAGE	SECONDARY VOLTAGE	50/60 Hz 1 PHASE		APPROXIMATE WEIGHT (Lbs/Kg)
			UL/cUL/CSA/NDM RATINGS (VA)	CE RATINGS (VA)	
9070T200D1	220/440 230/460 240/480	110 115 120	200	200	5.5 / 2.4
9070T200D2	240/480	24	200	200	5.5 / 2.4
9070T200D3	208	120	200	200	5.5 / 2.4
9070T200D4	277	120	200	200	5.5 / 2.4
9070T200D5	550 575 600	110 115 120	200	200	5.5 / 2.4
9070T200D12	440 460 480	220 230 240	200	200	5.5 / 2.4
9070T200D13	120	12/24	200	200	5.5 / 2.5
9070T200D14	208	24	200	200	5.4 / 2.4
9070T200D15	240/480	24/120	200	200	5.7 / 2.5
9070T200D22	480	277	200	200	5.5 / 2.4
9070T200D23	120/240	24	200	200	5.3 / 2.4
9070T200D24	110 115 120	110 115 120	200	200	5.5 / 2.4
9070T200D25	277	24	200	200	5.2 / 2.3
9070T200D31	220/440 230/460 240/480	110/220 115/230 120/240	200	200	5.5 / 2.4
9070T200D33	380/400/415	115/230	200	200	5.5 / 2.5
9070T200D36	600	12/24	200	200	5.5 / 2.5
9070T200D37	550 575 600	110/220 115/230 120/240	200	200	5.5 / 2.4
9070T200D52	380/400/415	12/24	200	200	5.5 / 2.5
9070T200D54	120/240	12/24	200	200	5.5 / 2.4
9070T200D55	110/220 115/230 120/240	110/220 115/230 120/240	200	200	5.5 / 2.4
9070T200D59	240/480	12/24	200	200	5.5 / 2.4
9070T200D60	277	120/240	200	200	5.5 / 2.4
9070T200D62	800	240	200	200	5.4 / 2.4



FILES/STANDARDS:
 UL/cUL FILE: E61236
 CSA FILE: LR37DS5
 CE: TUV CERTIFIED TO 81558
 NDM 117

200VA-CONTROL POWER TRANSFORMER
 9070 TYPE T
 CATALOG NUMBERS: FROM CHART



DWG# 5853
 ND.