



J:\wip\209\control online\5840.DWG 07/22/2008 12:13:06 PM

| CATALOG NUMBER | PRIMARY VOLTAGE | SECONDARY VOLTAGE | 50/60 Hz 1 PHASE | | APPROXIMATE WEIGHT (Lbs/Kg) |
|----------------|-------------------------------|-------------------------------|-----------------------------|-----------------|-----------------------------|
| | | | UL/cUL/CSA/NOM RATINGS (VA) | CE RATINGS (VA) | |
| 9070T50D1 | 220/440 230/460 240/480 | 110 115 120 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D2 | 240/480 | 24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D3 | 208 | 120 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D4 | 277 | 120 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D5 | 550 575 600 | 110 115 120 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D12 | 440 460 480 | 220 230 240 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D13 | 120 | 12/24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D14 | 208 | 24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D15 | 240/480 | 24/120 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D22 | 480 | 277 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D23 | 120/240 | 24 | 50 | 50 | 2.4 / 1.0 |
| 9070T50D24 | 110 115 120 | 110 115 120 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D25 | 277 | 24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D31 | 220/440 230/460 240/480 | 110/220 115/230 120/240 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D33 | 380/400/415 | 115/230 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D36 | 600 | 12/24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D37 | 550 575 600 | 110/220 115/230 120/240 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D52 | 380/400/415 | 12/24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D54 | 120/240 | 12/24 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D55 | 110/220 115/230 120/240 | 110/220 115/230 120/240 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D59 | 240/480 | 12/24 | 50 | 50 | 2.3 / 1.0 |
| 9070T50D60 | 277 | 120/240 | 50 | 50 | 2.5 / 1.1 |
| 9070T50D62 | 600 | 240 | 50 | 50 | 2.5 / 1.1 |



FILES/STANDARDS:
 UL/cUL FILE: E61239
 CSA FILE: LR37055
 CE: TUV CERTIFIED TO 61558
 NOM 117

50VA-CONTROL POWER TRANSFORMER
 9070 TYPE T
 CATALOG NUMBERS: FROM CHART

SQUARE D
 Schneider Electric

DWG# 5840
 NO.