


(CROUSE-HINDS RECEPTACLE)



TERMINAL LUGS ‡			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
30	#6 AWG	#12 AWG	AL
30	#6 AWG	#14 AWG	CU

SYMBOL	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1.00	25	1.38	35
D	1.25	32	1.75	45
E	1.50	38	2.00	51
F	2.00	51	2.50	64

DUAL DIMENSIONS: INCHES
MILLIMETERS

NOTES:
FINISH: SWITCHES - GRAY BAKED ENAMEL
CROUSE-HINDS RECEPTACLE - CAST ALUMINUM

UL LISTED - FILE E-2875
SHORT CIRCUIT CURRENT RATINGS:

10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.
200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R OR J FUSES.

WHEN MOUNTING THESE SWITCHES, ALLOW 4.00 IN / 102 MM MIN. CLEARANCE
BETWEEN ENCLOSURES FOR OPENING OF SIDE HINGED DOOR.

* USE BOTH OUTER SWITCHING POLES.

‡ LUGS SUITABLE FOR 80°C DR 75°C COPPER DR ALUMINUM CONDUCTORS.

CATALOG NUMBER	VOLTAGE RATINGS	AMPERE RATING	WIRING DIAG.	HORSEPOWER RATINGS											
				24VAC		480VAC				600VAC				250 VDC	
				MAX.	STD.	MAX.	STD.	MAX.	STD.	MAX.	STD.	MAX.	STD.	MAX.	
H361WC HU361WC	600VAC;250VDC 600VAC;250VDC	30 30	A B	-	3	5	7 1/2	15	7 1/2	-	20	10*	15*		
				5	10	-	-	10	20	15	-	30	-	10*	

HEAVY DUTY SAFETY SWITCHES
WITH RECEPTACLE
30 AMPERE-SERIES F6
ENCLOSURE - NEMA TYPE 1 GENERAL PURPOSE



QWC# 2216
NO.