



CIRCUIT BREAKER TERMINAL LUG DATA					
CIRCUIT BREAKER CATALOG NO. PREFIX	AMPERE RATING	CONDUCTORS PER PHASE	WIRE SIZE (AWG/KCML)		TYPE
			MAX.	MIN.	
LAL,LHL	125-400A	2	600	#1	AL OR CU
			250	#1	
Q4L	250-400A	2	600	#1	AL OR CU
			250	#1	

FIELD INSTALLABLE SOLID NEUTRAL ASSEMBLY AND GROUND KIT						
CATALOG NUMBER	MAXIMUM AMPERE RATING	NUMBER OF TERMINALS	CONDUCTORS PER TERMINAL	WIRE SIZE (AWG/KCML)		TYPE
				MAX.	MIN.	
SN400LA	400A	2	1 OR 2	600	#1	AL OR CU
				250	#1	
PKOGTA2	-	2	1	#2/0	#10	CU
				#2/0	#6	AL

FIELD INSTALLED CIRCUIT BREAKER DATA											
CIRCUIT BREAKER CATALOG NO. PREFIX	WIRING DIA.	AMPERE RATING	UL LISTED INTERRUPTING RATING RMS SYMMETRICAL AMPERES								FEDERAL SPECS. W-C-375B/GEN
			AC VOLTAGE				DC VOLTAGE				
			120	240	480Y/277	480	600	125	250	500	
LAL	A	125-400	42K	42K	30K	30K	22K	10K	10K	-	21A
	B	125-400	42K	42K	30K	30K	22K	10K	10K	-	21A
LHL	A	125-400	65K	65K	35K	35K	25K	10K	10K	-	23A
	B	125-400	65K	65K	35K	35K	25K	10K	10K	-	23A
LHL-DC	B	-	-	-	-	-	-	-	-	20K	-
Q4L	A	250-400	25K	25K	-	-	-	-	-	-	14B
	B	250-400	25K	25K	-	-	-	-	-	-	14B

NOTES:
 FINISH - NEMA/EEMAC TYPE 3,3R OR 12 - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL. NEMA/EEMAC TYPE 3,3R,4,4X & 5 OR 12 - TYPE 304 STAINLESS STEEL.
 UL LISTED - FILE E-136861 CSA LISTED - FILE # LL89067.
 SUITABLE FOR USE AS SERVICE EQUIPMENT WHEN NEUTRAL ASSEMBLY IS INSTALLED.
 ENCLOSURE SUPPLIED WITH DUAL COVER INTERLOCK
 NEUTRAL - INSULATED GROUNDABLE.
 THE SHORT CIRCUIT CURRENT RATING OF THIS ENCLOSED CIRCUIT BREAKER IS EQUAL TO THE INTERRUPTING RATING, AT THE SUPPLY VOLTAGE MARKED ON THE CIRCUIT BREAKER INSTALLED.

DUAL DIMENSIONS: INCHES
MILLIMETERS

CIRCUIT BREAKER ENCLOSURES 125-400 AMPERE ENCLOSURE-NEMA/EEMAC TYPE 3,3R OR 12 INDUSTRIAL NEMA/EEMAC TYPE 3,3R,4,4X,5,OR 12 STAINLESS STEEL	
DWG# 3078 No.	