



TERMINAL LUG DATA ‡			
AMPERES	MAX WIRE	MIN WIRE	TYPE
200	250 KCMIL	#6 AWG	CU/AL

DUAL DIMENSIONS: INCHES
MILLIMETERS

NOTES:
 FINISH - TYPE 316 STAINLESS STEEL
 UL LISTED - E2875
 CSA - FILE PER REFERENCE 158337 REPORT 1183171 (LL 89067).
 NEUTRALS - INSULATED GROUNDABLE
 SUITABLE FOR USE AS SERVICE EQUIPMENT
 SHORT CIRCUIT CURRENT RATINGS:
 10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.
 200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R OR J FUSES.
 ON 600V SWITCHES, 100,000 AMPERES MAX ON CORNER GROUNDED DELTA WHEN PROTECTED BY CLASS J OR R FUSES, 200 AMPERE MAX.
 ‡ LUGS SUITABLE FOR 75°C CONDUCTORS.
 # IF CORNER GROUNDED DELTA, USE OUTER SWITCHING POLES FOR UNGROUNDED CONDUCTORS.
 & IF CORNER GROUNDED DELTA, INSTALL NEUTRAL AND USE OUTER SWITCHING POLES FOR UNGROUNDED CONDUCTORS.
 ~ USE ANY TWO SWITCHING POLES.
 < MAX RATING

CATALOG NUMBER	VOLTAGE RATINGS	WIRING DIAG	HORSEPOWER RATINGS										250 VDC	600 VDC		
			240VAC				480VAC				600VAC					
			1Ø	3Ø	1Ø	3Ø	1Ø	3Ø	1Ø	3Ø	1Ø	3Ø				
H364SS	600VAC,600VDC	A	15~	25&	-	60&	25~	50&	50~	125&	30~	60	50~	150	40~	50~
HU364SS	600VAC,600VDC	B	-	-	15~	60&	-	-	60~	125&	-	-	50~	150	40~	50~

HEAVY DUTY SAFETY SWITCHES
 VISIBLE BLADE TYPE
 200 AMPERE-SERIES F6
 ENCLOSURE-NEMA TYPE 4, 4X AND 5 STAINLESS STEEL



DWG# 3334
NO.