TYPE	HANDLE LENGTH (INCHES)	HANDLE CAT. NUM.	SHAFT TYPE	SHAFT CAT. NUM.
LD1	6	LH6	STANDARD	LS8
LD4	6	LH6	LONG	LS13


	SION H RD SHAFT	DIMENSION H W/LONG SHAFT	
MIN	MAX	MIN	MAX
7.25/[184]	12.06/[306]	7.25/[184]	22.63/[575]


SHAFT LENGTH FORMULA: L=H-4.25/[108] MOUNTING DEPTH (H): MEASURED FROM THE CIRCUIT BREAKER MOUNTING SURFACE TO THE OUTSIDE OF THE ENCLOSURE DOOR.

IF THE SHAFT LENGTH IS GREATER THAN 10/[254] A SHAFT SUPPORT BRACKET MUST BE USED.

X: MINIMUM TO WALL OR BARRIER TO INSURE ADEQUATE WIRE BENDING SPACE TO LUG SURFACE WHEN THE MAXIMUM WIRE SIZE IS USED. REF. NEC 430-10

W/STANDARD 6 INCH HANDLE





CATALOG NUMBER: 9421-LD1, LD4, LD7 RATINGS: FOR USE W/POWERPACT D 3 POLE CIRCUIT BREAKER UL FILE/CCN: E6 MEETS STANDARDS: -E62922/DIHS2 WEIGHT: WIRE SIZE: TERMINAL TORQUE: -MOUNTING HWD: (2) M5 x .8 DIA SCREWS

OPERATING MECHANISM CLASS 9421 TYPE LD1, LD4, LD7 LZ400..., LZL400L... SQUARE D by Schneider Electric NO. 9421 LD_OUTLINE_001

Р

ىي

MAY 2009