


(CROUSE-HINDS RECEPTACLE)



TERMINAL LUGS ‡			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
60	#3 AWG	#12 AWG	AL
60	#3 AWG	#14 AWG	CU

DUAL DIMENSIONS: INCHES
MILLIMETERS

NOTES:
 FINISH: SWITCHES - GRAY BAKED ENAMEL
 CROUSE-HINDS RECEPTACLE - CAST ALUMINUM
 UL LISTED - FILE E-2875
 CSA CERTIFIED
 SHORT CIRCUIT CURRENT RATINGS:
 10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.
 200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R OR J FUSES.
 WHEN MOUNTING THESE SWITCHES, ALLOW 4.00 IN / 102 MM MIN. CLEARANCE
 BETWEEN ENCLOSURES FOR OPENING OF SIDE HINGED DOOR.
 * USE BOTH OUTER SWITCHING POLES.
 ‡ LUGS SUITABLE FOR 60°C OR 75°C CONDUCTORS ONLY.

CATALOG NUMBER	VOLTAGE RATINGS	AMPERE RATING	WIRING DIAG.	HORSEPOWER RATINGS										
				240VAC		480VAC				600VAC			250 * VDC	
				MAX.	STD.	MAX.		STD.		MAX.		STD.	MAX.	
H362AWC	600VAC; 250VDC	60	A	-	-	5	15	20	30	15	-	50	10	-
HJ362AWC	800VAC; 250VDC	60	B	10	20	-	-	25	50	-	30	60	-	10

HEAVY DUTY SAFETY SWITCHES
 WITH RECEPTACLE
 60 AMPERE-SERIES F7
 ENCLOSURE - NEMA TYPE 12, 3R



DMC# 31.33
 NO.