



TERMINAL LUG DATA †			
AMPERES	MAX WIRE	MIN WIRE	TYPE
100	#1/0 AWG	#14 AWG	CU
100	#1/0 AWG	#12 AWG	AL

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	VOLTAGE RATINGS	AMPERAGE RATINGS	WIRING DIAG	HORSEPOWER RATINGS ■															
				480VAC						600VAC						250 VDC		600 VDC	
				STD			MAX			STD			MAX			STD	MAX	STD	MAX
				1 Ø	2 Ø	3 Ø	1 Ø	2 Ø	3 Ø	1 Ø	2 Ø	3 Ø	1 Ø	2 Ø	3 Ø				
H363DSWA	600VAC,250VDC	100	A	10	-	25	30	-	60	-	-	30	-	-	75	20*	-	-	-
HU363DSWA	600VAC,250VDC	100	B	-	-	-	40	-	75	-	-	-	40	-	75	-	20*	-	-

NOTES:
FINISH: TYPE 304 STAINLESS STEEL.
UL LISTED - FILE E2875

SHORT CIRCUIT RATING:

10,000 AMPERES WHEN USED IN CONJUNCTION WITH CLASS H FUSES.

200,000 AMPERES WHEN USED IN CONJUNCTION WITH CLASS J OR R FUSES.

■ FOR SINGLE PHASE HP RATINGS USE 2 OUTER SWITCHING POLES.

*USE OUTER SWITCHING POLES.

†LUG SUITABLE FOR 60°C OR 75°C CONDUCTORS ONLY.

HEAVY DUTY SAFETY SWITCHES
VISIBLE BLADES
100 AMPERES - SERIES F7
ENCLOSURE - NEMA TYPE 4,4X AND 5
STAINLESS STEEL



DWG# 3183
NO.