

Counters

Totalising counters, predetermining counters
and totalising timers

Totalising counters

With mechanical display

Supply voltage	Number of display digits	Counting frequency	Type of reset to zero	Reference	Weight
V		Hz			kg
— 24	5	20	Manual	<u>XBK-T50000U10M</u>	0.100
	6	25	None	<u>XBK-T60000U00M</u>	0.030
		25	Manual	<u>XBK-T60000U10M</u>	0.150
	7	20	None	<u>XBK-T70000U00M</u>	0.100
	8	25	None	<u>XBK-T80000U00M</u>	0.150
— 48	5	20	None	<u>XBK-T50000U08M</u>	0.100
~ 115	5	10	Manual	<u>XBK-T50000U11M</u>	0.100
	6	10	Manual	<u>XBK-T60000U11M</u>	0.030

With LCD display

Supply voltage	Number of display digits	Counting frequency	Type of reset to zero	Reference	Weight
V		kHz			kg
Battery	8	7.5	Manual with electric locking	<u>XBK-T81030U33E</u>	0.050

Totalising timers

With mechanical display (max. display capacity : 99999.99 h)

Supply voltage	Number of display digits	Supply frequency	Type of reset to zero	Reference	Weight
V		Hz			kg
~ 24	7	50	None	<u>XBK-H70000004M</u>	0.060
~ 115	7	50	None	<u>XBK-H70000001M</u>	0.060
~ 230	7	50	None	<u>XBK-H70000002M</u>	0.060

With LCD display (max. display capacity : 999999.99 h)

Supply voltage	Number of display digits	Display mode	Type of reset to zero	Reference	Weight
V					kg
Battery	8	1/100 of an hour	Manual with electric locking	<u>XBK-H81000033E</u>	0.050



XBK-T50000U00M



XBK-T60000U00M



XBK-T60000U10M



XBK-T70000U00M



XBK-T80000U00M



XBK-T81030U33E



XBK-H70000000M



XBK-H81000033E

Counters

Totalising counters, predetermining counters
and totalising timers



XBK-P50100D●0M



XBK-P50100U●0M



XBK-P61●30G3●E



XBK-P62●30G3●E

Subtracting predetermining counters with mechanical display

Supply voltage	Number of display digits	Counting frequency	Number of presets	Type of reset	Reference	Weight
V		Hz				kg
--- 24	5	25	1	Manual	XBK-P50100D10M	0.200
				Manual and electric	XBK-P50100D20M	0.240

Adding predetermining counters with mechanical display

--- 24	5	25	1	Manual	XBK-P50100U10M	0.200
				Manual and electric	XBK-P50100U20M	0.240

Predetermining counters with LCD display

Supply voltage	Number of display digits	Counting frequency	Number of presets	Type of reset	Reference	Weight
V		kHz				kg
--- 24	6	5	1	Manual, electric and automatic	XBK-P61130G30E	0.150
			2	Manual, electric and automatic	XBK-P61230G30E	0.150
~ 115	6	5	1	Manual, electric and automatic	XBK-P61130G31E	0.250
			2	Manual, electric and automatic	XBK-P61230G31E	0.250
~ 230	6	5	1	Manual, electric and automatic	XBK-P61130G32E	0.250
			2	Manual, electric and automatic	XBK-P61230G32E	0.250

Predetermining counters with LED display

Supply voltage	Number of display digits	Counting frequency	Number of presets	Type of reset	Reference	Weight
V		kHz				kg
--- 24	6	5	1	Manual, electric and automatic	XBK-P62130G30E	0.150
			2	Manual, electric and automatic	XBK-P62230G30E	0.150
~ 230	6	5	1	Manual, electric and automatic	XBK-P62130G32E	0.250
			2	Manual, electric and automatic	XBK-P62230G32E	0.250