

CERTIFICATE FI 28899 A2



Our Ref. 278310

Product Shuttered socket-outlet
Type 101414, 101414-02, 101443, 101443-02
Trade mark LEXEL
Certificate Holder Schneider Electric Danmark A/S
 Wiring Device, Lautrupvang 1, DK-2750 BALLERUP, DENMARK

Manufacturer Schneider Electric Danmark A/S
 Wiring Device, Lautrupvang 1, DK-2750 BALLERUP, DENMARK

Technical information 16A, 250V~, IP20, IP21 and IP44. Class 0 and I

Other information Standard sheet CEE7 / III and CEE 7 / I and CEE7 / V.
 Flush-type two fold, Surface-type two fold and four fold. With shutters.
 Screw or screwless terminals. All colours.
 The design of the socket-outlet with base type 101414-02 and 101443-02 is consisting of plastic threads in socket for connecting cover to socket base.
 The design of the socket-outlet base type 101414 and 101443 is consisting of metal threads in socket for connecting cover to socket base.
 If the flush-type socket-outlet is to be installed in an unearthed metal box, the required clearance between live part and the metal box of minimum 4,5mm shall be met.
 If the flush-type socket-outlet is to be installed in an exclusively earthed metal box, the required clearance between live part and the metal box of minimum 3mm shall be met.

The product is certified according to the following standard(s) IEC 60884-1:2002 (Ed 3) + A1:2006 + A2:2013
 SFS 5610:2004 + A1:2008

Validity This certificate is valid until 21 November 2019 unless the standard in question has been amended or superseded with significant changes in requirements, in which case, SGS Fimko has the right to shorten the validity of the certificate based on the legislation of the European Union. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 21 August 2015

SGS Fimko Ltd

Signature



Matti Huttunen
 Certification Engineer

This certificate has 2 appendixes



This certificate is issued by the company under its General Conditions for Certification Services accessible at <http://www.sgs.fi/en/Terms-and-Conditions.aspx>. Attention is drawn to the limitations of liability defined therein and in the Test Report here above mentioned which findings are reflected in this certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Manufacturing sites

Elda-Eltra Elektrotechnika S.A
ul. Bugno 1, 78-400 SZCZECINEK,
POLAND

Additional information

The products have certificate 1508301 issued by Intertek Semko AB in accordance with the Nordic Certification Service system.



Socket- outlets flush-type two fold

Socket	Terminals	IP-Class	Mounting	Earth-type*	Design	Included parts (Cover parts etc)
101414 / 101414-02 101443 / 101443-02 (Flush-type 1,2)	Screw or Screwless terminals- Bridge connections / Through connections	20	Flush-type With Metal or Composite fixing frame semi flush	S	Trend	101392
				U		100465
				S	Decora	100464
				S		101433
				U	Senso	101063
				U		101284
				S	Artic	101281
				C		101283
				U	Neutral	101425
				S		101426
				S	Unica	101515
				U		101516
				S	Robust	101527
				U		101528
				C		101535
				F		101530
				S		101531
				U		101532
				C		101533
				F		101534
S	101610					
F	74220					
S	Lyx	100813				
S	Trend HP	100818				
U		100819				
S	Van-Geel	100969				
S	Trend Solid	101548, 101549, 101550***				
S	Artic Decor	101554 + outer frame***				
S		101367, 101364				
101414 / 101414-02 (Flush type 3)			Composite fixing frame and metal fixing frame semi flush	U	Renova	101365, 101364
				F		101470, 101364
				C		101471, 101364
101414 / 101414-02 (type 4)			Metal fixing frame 110368	S	Decora	101133
				S	Round	101155
101443 / 101443-02 (Flush type 3)			Full-flush with metal fixing frame	S	Trend	101578
				S	Trend Solid	101580, 101548, 101549***
				S	Artic	101581
				S	Artic Decor	101582 + outer frame***
				S	Exxact	35087
				S	M - SMART	NHA44968
101443 / 101443-02 (Flush type 1,2)			Semi flush with metal fixing frame	S	Exxact	35087
				U		42379
				S		42379 with pilot lamp
				S		42381
				U		42385
				S		42390
				S	M - SMART	NHA44972
				S	SYS - DESIGN	NHA50152
				S	SYS - ARTEC	

MPU

Appendix 2 to Certificate: 28899 A2

Socket-outlets surface-type two fold and four fold, Socket-outlet flush-type two fold

Socket	Terminals	IP-Class	Mounting	Earth-type*	Design	Included parts (Cover parts etc)
101414* / *101414-02	Screw or Screwless terminals-Bridge connections / Through connections	20	Surface-type	U	Trend	100542
				U	Quick-Rot 4W Exxact	101439
				U	ROT	100780
		21		S	Quick-Rot	100571
				S		100541
				S	Quick-Rot 4W Exxact	101083

101414 / 101414-02 101443* / 101443-02 101414-02		44	Flush-type Surface-type	U	Artic	101428	
				S	Artic	101429	
				S	ROT	100779	
		20		Surface-type	S	Aqua-Trend	101165
					S	Exxact NOTE 1	
					S	Robust	101604

NOTE 1 : Available with lockable lids.

* = Socket types	
Flush types	
1	Metallic "Standard"
2	Composite "Standard"
3	Composite "Renova"
4	Metallic "Diagonal"
5	Metallic "Full-Flush"
Surface types	
1	2-way with backplate
2	2-way without backplate
3	4-way composition

**= (Earth-type):	
U	Without earth contact
S	With side-earth contact
F	With pin-earth contact
C	With pin earth contact (CZ)

***=Changeable frames	
101549 may be exchanged by metal plate or glass plate	
Outer frame consisting of backframe of plastic, and a plate of plastic, metal or glass	

Flush-type socket-outlet types 1, 2 and 4 and surface-type socket-outlet types 1, 2 and 3 comply with the requirement for unintentional contact with test finger to current-carrying parts according to EN 60529 (IPX0B)

This certificate replaces previous certificate FI 28899 A1 dated 15 April 2015. Addition of new cover parts.

Our ref.no.

278310-3

01010