

Schneider Electric USA, Inc.

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

MA4IBAxX (e)

| <u>SPD Type</u> | <u>Volts (V)</u> | <u>AC/DC DC PV</u> | <u>Phase</u> | <u>Amps (A)</u> | <u>Ambient Min(°C)</u> | <u>Ambient Max(°C)</u> | <u>Mode</u> | <u>VPR (Vpk)</u> | <u>MLV (Vpk)</u> | <u>MCOV (V)</u> | <u>Vn (Vdc)</u> | <u>In (kA)</u> | <u>SCCR (kA)</u> | <u>Notes</u> |
|-----------------|------------------|--------------------|--------------|-----------------|------------------------|------------------------|-------------|------------------|------------------|-----------------|-----------------|----------------|------------------|--------------|
| 2CA (4-2) | 480/277 | AC | 3Y | n/a | -35 | 85 | L-N | 900 | - | 320 | - | 20 | 200 | 1 |
| | | | | | | | L-G | 900 | - | 320 | - | | | |
| | | | | | | | N-G | 900 | - | 320 | - | | | |

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21 and CSA Electrical Certification Notice 516/CSA C22.2 No. 8 13

(e) - Where xx can be 10, 12, 40, 60 or 90.

Note 1 - Suitable for Factory wiring only.

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2009-11-02

Last Revised: 2017-10-24

© 2017 UL LLC

