

Date : 03/29/2016

American Power Conversion  
Holdings Inc., Taiwan Branch  
3F No. 205, Sec. 3, Beixin Rd.  
231 Xindian Dist., New Taipei City  
Taiwan - R.O.C.  
Attn:

**Re. : CU US + Canada Certificate**

Type of Equipment : Uninterruptible Power Supply  
Model Designation : See Certificate  
Certificate No. : CU 72160730 0001  
File No. : 10055037 001  
Engineer/Contact : Andreas Klinker  
Standard(s) : UL 1778:2014  
CSA C22.2 NO. 107.3-14

Dear Madame or Sir,


The above referenced technical equipment has been tested and was found to be in compliance with the listed test requirement(s). Enclosed, please find the TUV Rheinland approval document No. CU 72160730 0001. It authorizes you to label the listed product(s) with the TUV Rheinland Mark identified in the approval document. For compliance, the Test Mark must be on the approved unit.

Your product is subject to regular factory follow-up inspections as well as annual certificate and factory registration fees.

In using the TUV Rheinland Mark you are obligated to comply with the TUV Rheinland of North America Service Agreement.

If we can be of any further assistance to you, please do not hesitate to contact us.

Sincerely yours,  
Certification Body

  
Dipl.-Ing. A. Klinker  
QA Certification Officer

Enclosure

# Certificate



Certificate no.

CU 72160730 01

**License Holder:**

American Power Conversion  
Holdings Inc., Taiwan Branch  
3F No. 205, Sec. 3, Beixin Rd.  
231 Xindian Dist., New Taipei City  
Taiwan

**Manufacturing Plant:**

International Precision  
Assemblies, Inc.  
Lot 6 Blk 8, Phase II Peza  
4106 Rosario Cavite  
Philippines

Test report no.: USA-AK 10055037 001

Client Reference:

Tested to: UL 1778:2014  
CSA C22.2 NO. 107.3-14

Certified Product: Uninterruptible Power Supply

License Fee - Units

Model Designation: 1) BN900Mxxxxxxxxxx  
2) BN900M-CAxxxxxxxxxx  
3) BE850M2xxxxxxxxxx  
(x=0-9, a-z, A-Z, +, \*, #, \_, -, blank)


7

Rated Voltage: 1)-3) AC 120V, 50/60Hz, 1Ø  
Rated Current: 1)-3) 12A  
Protection Class: I  
Output Raings: see Appendix (Constr. Data Form)  
Rated Ambient Temperature: 0-40°C max.

7

Appendix: 1, 1-12

Licensed Test mark:



Date of Issue  
(day/mo/yr)  
29/03/2016

# Certificate



Certificate no.

CU 72160730 02

**License Holder:**

American Power Conversion  
Holdings Inc., Taiwan Branch  
3F No. 205, Sec. 3, Beixin Rd.  
231 Xindian Dist., New Taipei City  
Taiwan

**Manufacturing Plant:**

International Precision  
Assemblies, Inc. Plant 2  
Lot 2 Blk 17, Phase IV Peza  
4106 Rosario Cavite  
Philippines

**Test report no.:** USA-AK 10055037 001

**Client Reference:**

**Tested to:** UL 1778:2014  
CSA C22.2 NO. 107.3-14


**Certified Product:** Uninterruptible Power Supply

**License Fee - Units**

Additional Manufacturing Plant: see above

(K752456)

**Licensed Test mark:**



**Date of Issue**

(day/mo/yr)  
29/03/2016