

iq.ul.com

Surge Protective Devices  
guide info

E314042

**Schneider Electric USA, Inc.**

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

**SSP09EMAxxy(d)\***

Permanently Connected

<u>SPD Type</u>	<u>Volts (V)</u>	<u>AC/DC DC PV</u>	<u>Phase</u>	<u>Amps (A)</u>	<u>Ambient Min(°C)</u>	<u>Ambient Max(°C)</u>	<u>Mode</u>	<u>VPR (Vpk)</u>	<u>MCOV (V)</u>	<u>In (kA)</u>	<u>SCCR (kA)</u>
2	600	AC	3D	n/a	-35	85	L-L L-G	2500 2500	840 840	20	200

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21 and CSA Electrical Certification Notice 516/CSA C22.2 No. 8 13

(d) - Where xx can be 10, 12, 16, 18, 20 (except for model SSP09EMAxxy) or 24 (except for model SSP09EMAxxy) and yy can be D, DF or F.

\* - Complementary Listed EMI Filters (FOKY), E314042.

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2015-04-30

Last Revised: 2017-10-24

© 2017 UL LLC

