


# Product End-of-Life Instructions

**TeSys D Thermal Overload Relay  
LRD 3365 to LRD 33696**



# Product End-of-Life Instructions – EoLI

## Product overview

**Product Range:** LRD 3365 to LRD 33696, LRD 4365 to LRD 4369

**Marketing Model/Name:** GDP:      1504    1508    1510    1512    1540    1554    1557    1573  
                                 3220    3302    3545    3550    5397    5923    6138    6140    6151    7810

**Size:** H x L x D in mm = **54 x 70 x 113**

**Weight** in g:

**Bewteen 704 and 1195**

## Purpose

The product family must be disposed according to the legislation of the country. This document is intended for use by end of life recyclers or treatment facilities. It provides the basic information to assure an appropriate end of life treatment for the components and materials of the product.

## Operations recommended for the end of life treatment


There are several steps to process the products at the end of life so as to recover components, materials or energy :

**Reuse → Separation for special treatment → Other dismantling → Shredding**

**CAUTION:** The product contains 9 plastic parts with brominated FR which are recommended to be treated separately during the End of Life operations.

## Product End-of-Life Instructions – EoLI

The components of the products that optimize the recycling performances are listed, identified and located hereunder.



| Recommendation    | Number on drawing | Components                       | Weight (in g) | Comment |
|-------------------|-------------------|----------------------------------|---------------|---------|
| Special treatment | 1                 | Plastic parts with brominated FR | 20.7          |         |

EoLI achieved with Schneider-Electric TT03 V5 procedure

### Schneider Electric Industries SAS

35, rue Joseph Monier  
 CS 30323  
 F- 92506 Rueil Malmaison Cedex  
 RCS Nanterre 954 503 439  
 Capital social 896 313 776 €

[www.schneider-electric.com](http://www.schneider-electric.com)