



### Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP SSH HTTP HTTPS SNMP RS232 LLDP Telnet SNTP MRP (Media Redundancy Protocol)
Port Ethernet	10/100BASE-TX - 8 port(s) copper cable 10/100/1000 BASE-TX - 2 port(s) copper (Gbit)
Maximum number of switches in cascade	Unlimited
Cybersecurity	Port hardening

### Complementary

Integrated connection type	Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable
Maximum cable distance between devices	100 M copper cable
Ethernet service	Configuration via web server VLAN Multicast filtering Data stream control IGMP Snooping SNMP-Traps and SYSLOG
Communication service	TFTP Quality of Service (QoS) Port monitoring Port mirroring Address conflict detection
Diagnostics run time	Signal contact Self test
Maximum number of switches in a ring	50
Redundancy	HiPER ring RSTP Redundant network coupling
[Us] rated supply voltage	12...48 V
Supply voltage limits	9.6...60 V DC SELV 18...30 V AC SELV

Power consumption in W	8.9 W
Electrical connection	Removable connector 6 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE UL RCM EtherNet/IP
Function available	Alarms (Traps) System information Report Trap log
Local signalling	1 dual colour LED (green/yellow) for P1 P2 power supplies 1 LED (red) for fault 1 dual colour LED (green/yellow) for ring manager 1 LED (green) for stand-by 1 LED per channel (green) for link status 1 LED per channel (yellow) for ACT Device status
Alarm output	1 voltfree contact 1 A
Alarm function	Power supply fault Data link status Redundancy ring fault Switch fault
Ethernet cabling system	TF switches
MTBF reliability	413698.0 H
Width	74 Mm
Height	131 Mm
Depth	111 Mm
Net weight	0.41 Kg

## Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	10...95 % non-condensing
IP degree of protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 508 EN/IEC 61131 IEC 61850-3
Product certifications	CE UL RCM ODVA EtherNet/IP BV GL

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	670 G
Package 1 Height	13 Cm
Package 1 width	16 Cm
Package 1 Length	24 Cm
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Weight	5.36 Kg
Package 2 Height	30 Cm
Package 2 width	40 Cm
Package 2 Length	60 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**