



High Density Metered Rack PDU AP7856

Metered rack power distribution unit solves rack-level power needs in a space efficient Zero-U form factor for high density applications.

32A 3-phase, 22kW (EMEA)



User Interface: On-board metering display and network connections



*Blade Application:
AP7856 installed in a
600mm wide NetShelter®
SX enclosure*

- Industry leading 0U low profile design allows access to hot swap blade components; first unit with max depth < 75mm
- Six (16A) magnetic-hydraulic circuit breaker protected outlet banks
- Comprehensive overload monitoring including current metering on each phase and on each of six load banks
- Network Management: Access, configure and manage units from remote locations via web, SNMP and telnet
- Flexible outlet configuration; (12) C19 receptacles for high density equipment and (6) C13s for ancillary equipment
- High temperature design for operation up to 60°C
- Color coded outlet banks for easy visual indication and load balancing

Outlet Bank Loads						
Load Thresholds [Amps]						
#	P	Name	Load	Over	Near Over	Low
1	L1-2	Outlet Bank 1	0.0 Amps	16	13	0
2	L1-2	Outlet Bank 2	0.0 Amps	16	13	0
3	L2-3	Outlet Bank 3	0.0 Amps	16	13	0
4	L2-3	Outlet Bank 4	0.0 Amps	16	13	0
5	L3-1	Outlet Bank 5	0.0 Amps	16	13	0
6	L3-1	Outlet Bank 6	0.0 Amps	16	13	0

Apply Cancel

Configuration		
Overload Alarm Threshold:	32	Amps
Near Overload Warning Threshold:	26	Amps
Low Load Warning Threshold:	0	Amps

Apply Cancel

User interface allows full user customization of alarms