

NetBotz 300

Cost-effective Security and Environmental Monitoring for Network Closets to Data Centers

Wall-mount monitoring for up to 4 external sensors and 1 embedded camera.





NetBotz is an active monitoring solution designed to protect against physical threats, environmental or human, that can cause disruption or downtime to IT infrastructure. This scalable suite of networked appliances, sensors, access controls and cameras is designed to safeguard environments ranging in size from network closets to data centers. The modular design allows for common sensors among the NetBotz appliances. Optional user-defined alerts can be sent in a variety of formats and are easily integrated into event escalation policies. For management of multiple NetBotz appliances, use InfraStruxure™ Central. InfraStruxure Central with Surveillance collects, organizes and distributes critical alerts while enabling a single view of multiple cameras, rapid search and retrieval of video and 'tagging' of important video clips.

NetBotz 300 Features

The NetBotz 300 offers the best value for security and environmental monitoring over the network. An integrated camera allows video surveillance and monitoring to record human activity. It provides temperature, humidity, door contact, dry contact, 0-5V, spot leak, vibration, and smoke monitoring. Additional features like integration with InfraStruxure Central, Power over Ethernet, and user-defined alerts make the NetBotz 300 the perfect unit to protect your IT assets from security and environmental threats. The NetBotz 300 can be used in network closets to data centers, but it is commonly installed in network closets and server rooms.

- > Environmental monitoring for up to 4 external APC universal sensors
- > Full-motion video camera
- > Adjustable alert thresholds
- > Integrates with InfraStruxure Central





NetBotz 300			
Product SKUS			
NetBotz Room Monitor 355 (w/o PoE Injector)		NBWL0355	
NetBotz Room Monitor 355 (with 120/240 V PoE Injector)		NBWL0356	
Technical Specifications			
Includes	Installation Guide, Documentation CD, Wall Mounting Bracket, USB Cable, PoE Injector (NBWL0356 only)		
Housing	Wall-mount, 210 mm H x 170 mm W x 94mm D		
Indicators	Alert, Power, Camera, Network Link, Temperature Display		
Integrated Camera	Images up to 1280x1024 resolution, 24-bit color, and up to 30 frames per second (fps)		
Integrated Sensors	Temperature, Airflow, Humidity, Dew point (calculated), Camera motion sensor		
APC Universal Sensors Supported	Temperature, Temperature / Humidity, Door Contact, Smoke, Spot Leak, Vibration, Dry Contact		
Connectors	Ethernet: 1 10/100 Base-T Ethernet Port (PoE enabled), (4) APC Universal Sensor Ports, 1 USB Configuration Port – Style B		
Protocols	TCP/IP, HTTP, HTTPS, SMTP, SNMP v1, v2c, and v3, DHCP, DNS, Socks v4 or V5 Proxy Server		
Management Interface	Internet Explorer® v 5.5 or later; Netscape® v 4.79, 5.0 or later; Mozilla® 1.3 or later; Firefox® 2.0 or later; NetBotz Advanced View Software		
Client System Requirements	Microsoft Windows (Vista Business and Enterprise, XP SP1-3, 2000), Red Hat EL4 and EL5, 512 MB RAM. Use of Advanced View interface requires a one-time download of the Sun™ Java Runtime Environment™.		
Operating Environment	Temperature: 0 - 45°C (32 – 113°F); Relative Humidity: 10-90% (non-condensing); For indoor use only, not designed for use in corrosive or caustic environments.		
Regulatory Approvals	NBWL0355: CE; FCC 47 CFR Part 15 Class A, ICES-003 Class A, AS/NZS CISPR 22, VCCI Class A, Low Voltage Directive 2006/95/EC, EMC Directive 204/108/EC, NBWL0356 Only: U.L, c-UL, GS-ul, IRAM, NOM, GOST, PSE		
Standard Hardware Warranty	Two Years		
Extended Warranty			
NBWN0001		Base - 2 Year Software Support Contract (NBWL0355/NBWL0455)	
NBWN0003		Extension - 1 Year Software Support Contract & 1 Year Hardware Warranty (NBWL0355/NBWL0455)	

