



TERMINAL LUGS DATA			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
600	(2) 500 KCMIL	(1) #3/0 AWG	AL/CU

SEISMIC NOTES:
USE (4) 3/8" DIA GRADE 5 STEEL MOUNTING BOLTS @ HOLES AA
MAX CONFIGURED WEIGHT 155 LB (AWK CATALOG NUMBERS)
157 LB (DS / SS CATALOG NUMBERS) FOR THE PURPOSE OF
DETERMINING SEISMIC ANCHORAGE REQUIREMENTS. FOR ALL OTHER
APPLICATIONS, CONTACT SCHNEIDER ELECTRIC.

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER		VOLTAGE RATINGS	WIRING DIAG.	HORSEPOWER RATINGS					
NEMA TYPE 12	NEMA TYPE 4,4X,5 STAINLESS STEEL			240VAC		480VAC		600VAC	
				STD.	MAX.	STD.	MAX.	STD.	MAX.
H326AWK	H326DS	240VAC	A	75	200	-	-	-	-
H326NAWK	H326NDS	240VAC	B	75	200	-	-	-	-
H366AWK	H366DS	600VAC;600VDC	A	-	-	150	400	200	500
H366NAWK	H366NDS	600VAC	B	-	-	150	400	200	500
HU366AWK	HU366DS	600VAC;600VDC	C	-	200	-	400	-	500
-	H366SS**	600VAC;600VDC	A	-	-	150	400	200	500
-	HU366SS**	600VAC;600VDC	C	-	-	150	400	200	500

NOTES:
FINISH - NEMA TYPE 12 GRAY BAKED ENAMEL
NEMA TYPE 4, 4X, 5 TYPE 304 & 316 STAINLESS STEEL
UL LISTED - FILE 3-154828
ALL NEUTRALS - INSULATED GROUNDABLE
SUITABLE FOR USE AS SERVICE EQUIPMENT
SHORT CIRCUIT CURRENT RATINGS:
10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.
200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R FUSES HAVING
CLASS R REJECTION KITS INSTALLED OR CLASS J FUSES.
** THESE DEVICES ARE 316 STAINLESS STEEL

HEAVY DUTY SAFETY SWITCHES
VISIBLE BLADE TYPE
600 AMPERE
ENCLOSURE - NEMA TYPE 12
NEMA TYPE 4, 4X, 5 STAINLESS STEEL

SQUARE D
by Schneider Electric

DWG# 1932S
NO.