



EVPU®

NOTIFIED BODY No. 1293

CERTIFICATE OF CONSTANCY OF PERFORMANCE

No. 1293 – CPR – 0879

In compliance with the *Regulation 305/2011/EU of the European Parliament and of the Council of 9 March 2011* (the Construction Products Regulation or CPR), this certificate applies to the construction product

Esmi Impresia Multicriteria Detector FFS06741003

For specifications see Annex to this certificate

placed on the market under the name or trade mark of

**Schneider Electric Buildings AB,
Mobilvägen 8, 223 62 Lund, Sweden**

and produced in the manufacturing plant

**Teletek Electronics JSC,
2, Iliyansko Shose Str., NPZ Voenna Rampa, 1220 Sofia, Bulgaria**

This certificate attests that all provisions concerning the assessment and verification of constancy of performance and the performances described in Annex ZA of the standard

**EN 54-5: 2017+A1: 2018,
EN 54-7:2018,
EN 54-17:2005, EN 54-17:2005/AC:2007**

under system 1 for the performance set out in this certificate are applied and that the factory production control conducted by the manufacturer is assessed to ensure the

constancy of performance of the construction product.

This certificate was first issued on March 14th, 2024 and will remain valid as long as neither the harmonised standard, the construction product, the AVCP methods nor the manufacturing conditions in the plant are modified significantly, unless suspended or withdrawn by the notified product certification body.

Nová Dubnica, March 14th, 2024




Michal Mišiak
Head of CB NB No. 1293

054908

EVPU a.s., Trenčianska 19, SK 018 51 Nová Dubnica, Slovak Republic, www.evpu.sk
Page 1 / 2 FCO 425-13 Rev.2

Annex to Certificate No. 1293 - CPR – 0879 from March 14th, 2024

General information

Esmi Impresia Multicriteria Detector (FFS06741003) is an addressable combined (temperature and optical-smoke) detector with built-in isolator module, designed for installing in addressable fire alarm systems with Esmi ELC loop controller supporting Schneider Electric communication protocol.

The detector is compatible with Esmi Impresia Standard Base (FFS06741018) and Esmi Impresia Standard Base High Profile (FFS06741028).

The address setting is done by the panel, QR code or handheld addressing device.

Technical specifications


Operating voltage range	16-32V DC (Nom. 27V DC)
Class (EN 54-5)	A1/R
Sensitivity level (EN 54-7)	Normal
Dimensions	103x48.3mm
Weight	~ 94,5g
Supported communication protocol	Esmi ELC

Essential characteristics	Harmonised technical specification			Performance
	EN 54-5: 2017+A1: 2018	EN 54-7: 2018	EN 54-17: 2005 EN 54-17: 2005/ AC:2007	
Operational reliability	cl. 4.2.1, 4.2.2, 4.2.3=N/A, 4.2.4, 4.2.5, 4.2.6=N/A, 4.2.7	cl. 4.2.1 to 4.2.8	cl. 4	Pass
Nominal activation conditions / Sensitivity	cl. 4.3.1 to 4.3.6	cl. 4.3.1 to 4.3.3	---	Pass
Response delay (response time)	cl. 4.4.1=N/A, 4.4.2	cl. 4.4.1, 4.4.2	---	Pass
Tolerance to supply voltage	cl. 4.5.1	cl. 4.5	---	Pass
Performance parameters under fire conditions	---	cl. 4.6	cl. 5.2	Pass
Durability of Nominal activation condition / Sensitivity: Temperature resistance	cl. 4.6.1.1, 4.6.1.2=N/A	cl. 4.7.1.1, 4.7.1.2	cl. 5.4, 5.5	Pass
Durability of Nominal activation condition / Sensitivity: Humidity resistance	cl. 4.6.2.1, 4.6.2.2	cl. 4.7.2.1, 4.7.2.2	cl. 5.6, 5.7	Pass
Durability of Nominal activation condition / Sensitivity: Corrosion resistance	cl. 4.6.3	cl. 4.7.3	cl. 5.8	Pass
Durability of Nominal activation condition / Sensitivity: Vibration resistance	cl. 4.6.4.1 to 4.6.4.4	cl. 4.7.4.1 to 4.7.4.4	cl. 5.9 to 5.12	Pass
Durability of Nominal activation condition / Sensitivity: Electrical stability	cl. 4.6.5	cl. 4.7.5	cl. 5.3, 5.13	Pass

History of certification

No.	Certificate No.	Description	Date of issue
1	1293-CPR-0773	Original certificate issued	April 1 st , 2021
2	1293-CPR-0773 Rev.1	Testing according to the new edition of standards	September 14 th , 2022
3	1293-CPR-0879	New company name and location New location of place of production	March 14 th , 2024

Nová Dubnica, March 14th, 2024



Michal Mišiak
Head of CB NB No. 1293