



TERMINAL LUGS ‡			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
60	# 4 AWG	# 14 AWG	CU

(CROUSE HINDS RECEPTACLE)

OBSOLETE 02/2006
WILLHOITE

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	VOLTAGE RATINGS	WIRING DIAG.	HORSEPOWER RATINGS																						
			240VAC				480VAC				600VAC				250VDC	600VDC									
			STD.	MAX.	STD.	MAX.	STD.	MAX.	STD.	MAX.	MAX.	STD.	MAX.												
H362DSWC	600VAC;600VDC	A	1Ø	3Ø	1Ø	3Ø	2Ø	3Ø	1Ø	2Ø	3Ø	2Ø	3Ø	1Ø	2Ø	3Ø	MAX.	STD.	MAX.						
HU362DSWC	600VAC;600VDC	B	-	-	-	10	20	-	15	-	20	-	30	50*	-	15	-	25	-	50	60*	-	10	25	30

- NOTES: FINISH - NEMA TYPE 3,3R,4,4X,5 OR 12 - TYPE 304 STAINLESS STEEL
 UL LISTED - FILE E-2875
 FOR SERVICE EQUIPMENT USE OR WHERE NEUTRAL IS REQUIRED, ORDER KIT NUMBER H60SNC.
 SHORT CIRCUIT CURRENT RATINGS:
 10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.
 200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R, T OR J FUSES.
 * USE 75°C #4 CU WIRE
 † NOT SUITABLE FOR USE AS SERVICE EQUIPMENT
 ‡ LUGS SUITABLE FOR 60°C OR 75°C COPPER CONDUCTORS ONLY.

HEAVY DUTY SAFETY SWITCHES
 VISIBLE BLADE TYPE
 60 AMPERE
 ENCLOSURE - NEMA TYPES 3, 3R, 4, 4X, 5 OR 12
 STAINLESS STEEL



DWG# 3132
NO.