

Certificate




for European Product Safety

Reference No. 1719990

Membrane


| | |
|---|---|
| Type designation | TET 3-5, TET 3-5C, TET 5-7, TET 5-7C, TET 7-10, TET 7-10C, TET 10-14, TET 10-14C, TET 14-20, TET 14-20C, TET 20-26, TET 20-26C, TET 26-35, TET 26-35C |
| Certificate holder | Schneider Electric Industries SAS 35 rue Joseph Monier FR 92500 Rueil-Malmaison FRANCE |
| The product complies with the standard(s) | EN 60670-1:2005+A1:2013 |
| Date of expiry | 27 January 2022 |
| EU Directive information | According to the principle of presumption of conformity, this certificate constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU. |

Additional information in Appendix.

| | | | |
|--------------------|---|-------|------------------------------|
| Certification Body | Intertek Semko AB, Product Certification | Place | Kista - Stockholm |
| Signed |  Paul Klemets | Date | 26 April 2018 Page 1 of 3 |

This certificate is issued in accordance with the terms and conditions set out in the Appendix.

**Intertek
Appendix***Reference No. 1719990**Technical data*

| | |
|-----------------------------|---|
| <i>Type designation</i> | TET 3-5, TET 3-5C, TET 5-7, TET 5-7C, TET 7-10, TET 7-10C, TET 10-14, TET 10-14C, TET 14-20, TET 14-20C, TET 20-26, TET 20-26C, TET 26-35, TET 26-35C |
| <i>IP-Class</i> | IP67 |
| <i>Trade mark</i> | THORSMAN or  |
| <i>Product information:</i> | <p>TET 3-5 Grey EPDM or TET 3-5C black CR membrane inlet for cables with diameter 3-5 mm for 12-13 mm mounting hole and 0,5-2 mm wall thickness.</p> <p>TET 5-7 Grey EPDM or TET 5-7C black CR membrane inlet for cables with diameter 5-7 mm for 16-17 mm mounting hole and 1-4 mm wall thickness.</p> <p>TET 7-10 Grey EPDM or TET 7-10C black CR membrane inlet for cables with diameter 7-10 mm for 19-20 mm mounting hole and 1-4 mm wall thickness.</p> <p>TET 10-14 Grey EPDM or TET 10-14C black CR membrane inlet for cables with diameter 10-14 mm for 23-24 mm mounting hole and 1-4 mm wall thickness.</p> <p>TET 14-20 Grey EPDM or TET 14-20C black CR membrane inlet for cables with diameter 14-20 mm for 29-30 mm mounting hole and 1-4 mm wall thickness.</p> <p>TET 20-26 Grey EPDM or TET 20-26C black CR membrane inlet for cables with diameter 20-26 mm for 38-39 mm mounting hole and 1-4 mm wall thickness.</p> <p>TET 26-35 Grey EPDM or TET 26-35C black CR membrane inlet for cables with diameter 26-35 mm for 48-49 mm mounting hole and 1-4 mm wall thickness.</p> |

This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.



Intertek
Appendix

Reference No. 1719990


Manufacturing site(s) ELTEC
7-Th Piatra Craiului St.
Negoiesti, Brazi
Prahova county 107086
ROMANIA

According to the principle of presumption of conformity, this certificate, which includes production control, constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

This certificate replaces previously issued ref. No. 1121398 dated 27 January 2012.
A new certificate has been issued on account of renewal of S-certificate and updated standard.

Certification Body Intertek Semko AB, Product Certification Place Kista - Stockholm

Signed 
Paul Klemets Date 26 April 2018

This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.

AMP