


TYPE 4,4X,5 AND 12  
NO KNOCKOUTS



TERMINAL LUG DATA			
AMPERES	MAX WIRE	MIN WIRE	TYPE
400	(1) 600 KCMIL OR	(1) 1/0 AWG OR	AL/CU
	(2) 300 KCMIL	(2) 1/0 AWG	

DUAL DIMENSIONS: INCHES  
MILLIMETERS

NOTES:  
FINISH - TYPE 12 GRAY BAKED ENAMEL  
4, 4X, 5 TYPE 304 & 316 STAINLESS STEEL  
CSA CERTIFIED - FILE #97047  
ALL NEUTRALS - INSULATED GROUNDABLE  
FUSIBLE SWITCHES ARE SUITABLE FOR USE AS SERVICE EQUIPMENT  
SHORT CIRCUIT CURRENT RATINGS:

10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.  
200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R FUSES HAVING  
CLASS R REJECTION KITS INSTALLED OR CLASS J FUSES.  
SUFFIX E1 OR E2 - FACTORY INSTALLED ELECTRICAL AUXILIARY INTERLOCK.  
SUFFIX J1 - VOLTAGE MONITORS FOR LOAD SIDE.  
SUFFIX J2 - VOLTAGE MONITORS FOR LOAD/LINE SIDE.  
SUFFIX VW - FACTORY INSTALLED VIEWING WINDOW.

CATALOG NUMBER			VOLTAGE RATINGS	WIRING DIAG	HORSEPOWER RATINGS							
TYPE 12	TYPE 4,4X,5 304 STAINLESS STEEL	TYPE 4,4X,5 316 STAINLESS STEEL			240VAC		480VAC		600VAC		250 VDC	600 VDC
					STD	MAX	STD	MAX	STD	MAX	MAX.	MAX.
CH325NAWK	CH325NDS	CH325NSS	240VAC	B	50	125	-	-	-	-	50	-
CH365NAWK	CH365DS	H365SS	600VAC;600VDC	A	-	-	100	250	125	350	-	50
CH365NAWK	CH365NDS	H365NSS	600VAC	B	-	-	100	250	125	350	-	-
CHU365NAWK	CHU365DS	HU365SS	600VAC;600VDC	C	-	125	-	250	-	350	-	50

HEAVY DUTY SAFETY SWITCHES  
VISIBLE BLADE TYPE  
400 AMPERES  
ENCLOSURE - TYPE 12  
TYPE 4, 4X, 5 STAINLESS STEEL;



DWG# 2147C  
NO.