



ÖVE-CERTIFICATE

including the entitlement to use the Austrian Safety Mark



Certificate No.: **4900-046-12**

Valid from: 2024 06 23
until: 2025 07 09

The Austrian Electrotechnical Association (OVE) hereby grants the right to the company mentioned below to label the listed products with the Austrian Safety Mark.

Certificate holder: **Schneider Electric Industries SAS**
35, rue Joseph Monier
92500 Rueil-Malmaison
France

Product: **Two pole socket outlet with side earthing contacts**

The products submitted by the applicant were type tested in accordance with the requirements of the technical standards and specifications listed in this certificate. OVE certifies the conformity of the listed products and those products manufactured strictly identical to the submitted ones (EN ISO/IEC 17067, Conformity Assessment Scheme Type 5).

The manufacturing process and the products are subject to ongoing surveillance based on harmonized European procedures. This certificate has been issued under the presumption and conditional on the fact that the certificate holder holds all necessary legal rights with regard to the product, presented for the testing and certification.

Results of testing are shown in file No(s): **TGM-VA EE 33387F, TGM-VA EE 33387E**

Österreichischer Verband für Elektrotechnik
Head of OVE Certification

T. Neumayer
Digitally signed by T. Neumayer
Email=t.neumayer@ove.at

Dipl.-Ing. T. Neumayer

Wien, 2024 06 25



OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.



Manufacturer:

Schneider Electric Industries SAS
35, rue Joseph Monier
92500 Rueil-Malmaison
France

Factory location(s):

Merten GmbH
Fritz Kotz Straße 8
51674 Wiehl-Bornig
Germany

Tested and certified according to:

ÖVE/ÖNORM IEC 60884-1:2005-09-01
ÖVE/ÖNORM E 8684-1:2010-03-01

Product: Two pole socket outlet with side earthing contacts

Type designation:

Rating:

Trademark:

230

Rated voltage: AC 250 V
Rated current: 16 A
SCHUKO socket-outlet
screwless terminals, flush-type
see typelist

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

Typelist

System M (Thermo/Duro)

230/2371

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert

MERTEN/SCHNEIDER ELECTRIC

230/2373

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2376

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with hinged lid

MERTEN/SCHNEIDER ELECTRIC

230/2376 IP44

Rated voltage: AC 250 V
Rated current: 16 A
IP 44
Insert with hinged lid and gasket

MERTEN/SCHNEIDER ELECTRIC

230/2374 IP44

Rated voltage: AC 250 V
Rated current: 16 A
IP 44
Insert with hinged lid and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2374

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with hinged lid and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2300

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2300-35 (M-Creativ)

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with transparent cover and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

230/2301

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet

MERTEN/SCHNEIDER ELECTRIC

230/2309

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Central plate with labelling field and control light incl. Modul Mxx2003-0004

MERTEN/SCHNEIDER ELECTRIC

230/2309

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with labelling field and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2474

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and labelling field

MERTEN/SCHNEIDER ELECTRIC

230/2485

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert 45° with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2496

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert 45° with labelling field and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2470 (Atelier-M)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet

MERTEN/SCHNEIDER ELECTRIC

230/2471 (Atelier-M)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2472 (1-M)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

230/2473 (1-M)

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Socket-outlet with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2334

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Central plate with light opening and LED display lighting incl. Modul Mxx2334

MERTEN/SCHNEIDER ELECTRIC

230/2315

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert lockable with hinged lid and improved protection against accidental protection

System Design (Thermo/Duro)

230/2375

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert

MERTEN/SCHNEIDER ELECTRIC

230/2377

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2372

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with hinged lid

MERTEN/SCHNEIDER ELECTRIC

230/2379

Rated voltage: AC 250 V
Rated current: 16 A
IP 20
Insert with labelling field

MERTEN/SCHNEIDER ELECTRIC

230/2378 IP44

Rated voltage: AC 250 V
Rated current: 16 A
IP 44
Insert with hinged lid, gasket and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

230/2378

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2306

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact, Tracent

MERTEN/SCHNEIDER ELECTRIC

230/2379

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with labelling field and control light (Modul Mxx2003-0004)

MERTEN/SCHNEIDER ELECTRIC

230/2308

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with labelling field and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2478

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and labelling field

MERTEN/SCHNEIDER ELECTRIC

230/2476

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert 45° with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2477

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert 45° with labelling field and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

System Design (Thermo/metal)

230/NHA5191702 (thermo)

230/NHA5200102 (metal)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

230/NHA2922902 (thermo)

230/NHA2922002 (metal)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/NHA5191902 (thermo)

230/NHA2922002 (metal)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet with labelling filed

MERTEN/SCHNEIDER ELECTRIC

230/NHA5191802 (thermo)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with Floor Light and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/NHA5195702 (thermo)

230/NHA5195702 (metal)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/NHA5195702/PHA8168102 (thermo)

230/NHA5195702/NHA5200202 (metal)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and improved protection against accidental contact and labelling filed

MERTEN/SCHNEIDER ELECTRIC

230/NHA5195702 IP44 (thermo)

230/NHA5195702 IP44 (metal)

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid, gasket and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/NHA2920902 (thermo)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert for special electric circuits with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/NHA5191902 (thermo)

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert for special electric circuits with improved protection against accidental contact and labelling filed

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

AQUADESIGN

230/2330 IP44

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2335

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2330 IP44

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid, labelling field and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

230/2330 IP44

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid, lockable and improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

Renova

230/EAV54699

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

Anti vandalism

230/S1B7217902

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet with improved protection against accidental contact

MERTEN/SCHNEIDER ELECTRIC

OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.