



ATTESTATION of conformity with European Directives

BV LCIE CHINA Number N°2266AS07SDEC46154
Product EVlink Home Smart
Reference See model list
Issued to Schneider Electric Industries SAS
Address 35, rue Joseph Monier 92500 Rueil Malmaison France
Manufacturer Schneider Electric Industries SAS
Technical characteristics See model list

The submitted sample of the above equipment has been tested for **CE** marking according to following European Directive and following standards:
RE Directive 2014/53/EU

Standards	Report number	Report date
Article 3.1(a) Safety: EN IEC 61851-1:2019	SDEC-ESH-P22031994	23/07/2022
Article 3.1(a) Health: EN 62311:2008 EN 50665:2017	SDEC-ESH-P22031994B-3	04/07/2022
Article 3.1(b) EMC: EN 301 489-1 V2.2.3 (2019-11) EN 301 489-17 V3.2.4 (2020-09) EN IEC 61851-21-2:2021 EN IEC 61000-6-1:2019 EN IEC 61000-6-3:2021	SDEC-ESH-P22031994B-1 WPHE220899 WPHE220900	04/07/2022 01/08/2022 01/08/2022
Article 3.2 Radio: EN 300 328 V2.2.2 (2019-07)	SDEC-ESH-P22031994B-2	04/07/2022

The referred test report(s) show that the product complies with standard(s) recognized as giving presumption of compliance with the essential requirements in the specified European Directive

This verification does not imply assessment of the production of the product

The **CE** marking may be affixed if all relevant and effective European Directives with **CE** are applicable

Shanghai (P.R. China), Aug 2th, 2022



Denis SUN
Product Line Manager

This document shall not be reproduced, except in full, without the written approval of BV LCIE China. Information given in this document, are related to the tested specimen of the described electrical sample.

Version: 7.0 / Feb.10, 2021

Page 2 of 2

Model list

Model name	Input and output ratings	Connection method	Radio functions	Protection class	Mass
EVH4A03N2	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30°C - 50°C	Case B T2 socket	Wifi	IP54 Class I	3.7kg
EVH4A07N2	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30°C - 50°C	Case B T2 socket	Wifi	IP54 Class I	3.7kg
EVH4A11N2	Three phase, 11kw 380-415V, Max 16A,50Hz, -30°C - 50°C	Case B T2 socket	Wifi	IP54 Class I	3.7kg
EVH4A03NC	Single phase, 3.7kw 220-240V, Max 16A,50Hz, -30°C - 50°C	Case C Cable length:5m	Wifi	IP55 Class I	5.2kg
EVH4A07NC	Single phase, 7.4kw 220-240V, Max 32A,50Hz, -30°C - 50°C	Case C Cable length:5m	Wifi	IP55 Class I	5.2kg
EVH4A11NC	Three phase, 11kw 380-415V, Max 16A,50Hz, -30°C - 50°C	Case C Cable length:5m	Wifi	IP55 Class I	5.2kg