

# CERTIFICATE

Issued to:  
Applicant:  
**Schneider Electric Industries SAS**  
35 Rue Joseph Monier  
92500 Rueil-Malmaison, France

Licensee:  
**Schneider Electric Industries SAS**  
35 Rue Joseph Monier  
92500 Rueil-Malmaison, France

Product : two-pole socket-outlets  
Trade name(s) : MERTEN or Schneider Electric  
Type(s)/model(s) : 230/2270/- and 270/2270/-

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019 and NEN-IEC 60884-1:2019/A2:2019
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2142166


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 9 September 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-124715

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



MT Tonsi  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: two-pole socket-outlets
Trade name(s)	: MERTEN or Schneider Electric
Type(s)/model(s)	: 230/2270/- and 270/2270/-
Method of mounting	: flush-type, screw-fixing
Cover	: plural cover plate
Rated current	: 16 A
Rated voltage	: 250 V~
Design	: optional safety socket-outlet
Programm	: system M, M-Creativ and Exxact
Markings	: -tradenname, series-indication and electrical ratings on the base -tradenname and suffix for the cover on these parts

**Product data – type 230/2270/-**

Terminals : screwless terminals

**Product data – type 270/2270/-**

Terminals : screw terminals

**TESTS****Test requirements**

NEN 1020:2019  
NEN-IEC 60884-1:2019  
NEN-IEC 60884-1:2019/A1:2019  
NEN-IEC 60884-1:2019/A2:2019

**Test result**

The test results are laid down in DEKRA test file 226504800.

**Additional information**

This certificate replaces certificate No. 2157702.08 which we hereby declare invalid.

**Conclusion**

The examination proved that all requirements were met.

**Factory location**

Merten GmbH  
Fritz-Kotz-Strasse 8  
51674 Wiehl-Bomig, Germany



230 without earth socket deep plug in screwless, with white base part, with claw fixing (used for System M and M-Creativ)



230 without earth socket deep plug in screwless, with green base part, with or without claw fixing (used for Exxact)

**System M**



2270 socket outlet wo earth screwless with shutter deep plug-in

**Exxact**



2270 socket outlet wo earth screwless with shutter deep plug-in

Color variants System M:



polar white



active white



white



anthracite



aluminium

**M - Creativ**



2000-35 socket outlet wo earth screwless with shutter deep plug-in



270

without earth socket deep plug in screw-terminal with white base part, with claw fixing (used for System M)



270

without earth socket deep plug in screw-terminal with green base part without claw fixing (used for Exxact)

**System M**



2270

socket outlet wo earth screw-terminal deep plug-in, with or without shutter

Color variants System M:



polar white



active white



white



anthracite



aluminium

**Exxact**




2270





socket outlet wo earth screw-terminal with shutter deep plug-in

**System M (Thermo + Duro)**


**M-Plan II**





**M-Plan**




**M-PLAN Metal**



**M-Plan real glass**



**1 M**



**Elegance**

