

# CERTIFICATE

Issued to:  
Applicant:  
**Schneider Electric Industries SAS**  
35 rue Joseph Monier  
92500 Rueil-Malmaison, France

Product : Socket-outlets (2-pole) for fixed installation with USB charger  
Trade name(s) : MERTEN or SCHNEIDER ELECTRIC  
Type(s)/model(s) : EE4227

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard IEC 60884-1:2002, IEC 60884-1:2002/A1:2006, IEC 60884-1:2002/A2:2013, DIN VDE 0620-1:2016, DIN VDE 0620-1:2016/A1:2017, NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019, NEN-IEC 60884-1:2019/A2:2019, SFS 5610:2015, SFS 5610:2015/A11:2016, SS-IEC 60884-1:2013, SS 4280834:2013, NEK IEC 60884-1:2002 + A1:2006, NEK IEC 60884-1:2002 + A1:2006/A2:2013, NEK 502:2016, UNE 20315-1-1:2017, EN IEC 61558-1:2019, EN 61558-2-16:2009, EN 61558-2-16:2009/A1:2013, EN 62368-1:2014 and EN 62368-1:2014/A11:2017
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 4339768
- the licensee is registered with the number 21934


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 27 May 2020 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 35-114017

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



K. Lin  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: Socket-outlets (2-pole) for fixed installation with USB charger
Trade name(s)	: MERTEN or SCHNEIDER ELECTRIC
Type(s)/model(s)	: EE4227
Method of mounting	: flush-type
Rated current	: 16 A
Rated voltage	: 250 V~
USB charger	: output: 5 Vdc, Max. 2,4A
Earthing	: with side earthing-contacts
Design	: rewirable, socket-outlets for fixed installation (with shutters)
Standard sheet	: III of CEE 7
Degree of protection	: IP20
Terminals	: screwless terminals (rigid conductors and flexible conductors)
Description	: body of thermoplastic material, provided with USB charger
Markings	: are shown on the body

**TESTS****Test requirements**

IEC 60884-1:2002  
IEC 60884-1:2002/A1:2006  
IEC 60884-1:2002/A2:2013  
DIN VDE 0620-1:2016  
DIN VDE 0620-1:2016/A1:2017  
NEN 1020:2019  
NEN-IEC 60884-1:2019  
NEN-IEC 60884-1:2019/A1:2019  
NEN-IEC 60884-1:2019/A2:2019  
SFS 5610:2015  
SFS 5610:2015/A11:2016  
SS-IEC 60884-1:2013  
SS 4280834:2013  
NEK IEC 60884-1:2002 + A1:2006  
NEK IEC 60884-1:2002 + A1:2006/A2:2013  
NEK 502:2016  
UNE 20315-1-1:2017  
EN IEC 61558-1:2019  
EN 61558-2-16:2009  
EN 61558-2-16:2009/A1:2013  
EN 62368-1:2014  
EN 62368-1:2014/A11:2017

**Test result**

The test results are laid down in DEKRA test file 436418600 and 436418700.

**Additional information**

The list of components is laid down at test report 4364186.50.

**Conclusion**

The examination proved that all requirements were met.

**Factory locations**

The factory locations are registered with the numbers 313419 and 21161.

Trade name(s) : SCHNEIDER ELECTRIC stands for 

MERTEN stands for ***merten***