



DRY-TYPE TRANSFORMERS  
3-6 KVA 3Ø 60HZ  
ENCAPSULATED  
NEMA 3R ENCLOSURE TYPE



480 DELTA - 208Y/120 CONNECT TO TAPS	
PRIMARY VOLTS	2-5% FCBN
504	-
492	-
480	H1, H2, H3
468	-
456	H4, H5, H6
432	H7, H8, H9

480 DELTA - 240 DELTA CONNECT TO TAPS	
PRIMARY VOLTS	2-5% FCBN
480	H1, H2, H3
468	-
456	H4, H2, H5
444	-
432	H6, H2, H7

600 DELTA - 208Y/120	
PRIMARY VOLTS	CONNECT TO TAPS
600	H1, H2, H3
570	H4, H5, H6
540	H7, H8, H9

SEISMIC QUALIFICATION:  
TO BE COMPLIANT WITH THE SEISMIC REQUIREMENTS OF ASCE/SEI7, THIS UNIT HAS BEEN QUALIFIED BY SHAKE TABLE TESTING THROUGH SELF CERTIFICATION TO ICC ES AC156. THE ENCLOSURE SHOWN ABOVE IS 12C. CONTACT YOUR LOCAL SCHNEIDER ELECTRIC/SQUARE D REPRESENTATIVE FOR RELATED QUESTIONS.

DUAL DIMENSIONS: INCHES  
MILLIMETERS

KVA	CATALOG NUMBERS			GUAR. SOUND LEVEL IN DB'S	WGT LBS
	480 DELTA-208Y/120	480 DELTA-240 DELTA	600 DELTA-208Y/120		
3	3T2F	-	-	40	125
6	6T2F	6T5F	6T7F	40	150

NOTES: UL LISTED  
115°C RISE ABOVE 40°C AMBIENT, CLASS 180 INSULATION  
MINIMUM CLEARANCE OF 6.00IN / 152MM BETWEEN VENT OPENINGS,  
WALL OR OTHER OBSTRUCTION.

DRY-TYPE TRANSFORMER  
3-6KVA 3PH 60HZ  
ENCAPSULATED  
NEMA 3R ENCLOSURE TYPE

SQUARE D  
by Schneider Electric

DWG# 3544  
NO.