

CERTIFICATE

Issued to:
Applicant:
Schneider Electric Industries SAS
31 Rue Pierre Mendes France
38320 Eybens, France

Product : surge protective devices
Trade name(s) : SCHNEIDER ELECTRIC
Type(s)/model(s) : 16315 - C1 25-350, 16316 - C2 40-350, 16317 - C1 Neutral-350,
16329 - PRD1 25r 1P, 16330 - PRD1 25r 1P+N, 16331 - PRD1 25r 3P and
16332 - PRD1 25r 3P+N

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN 61643-11:2012 and EN 61643-11:2012/A11:2018
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 900469
- the licensee is registered with the number 676000


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 20 January 2026 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-167136

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



Henk Schendstok
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: surge protective devices
Trade name(s)	: SCHNEIDER ELECTRIC
Type(s)/model(s)	: 16315 - C1 25-350, 16316 - C2 40-350, 16317 - C1 Neutral-350, 16329 - PRD1 25r 1P, 16330 - PRD1 25r 1P+N, 16331 - PRD1 25r 3P and 16332 - PRD1 25r 3P+N
SPD type/class	: 1/I and 2/II
Voltage protection level (Up)	: 1,5 kV
Short-circuit current rating (Isc cr)	: 25 kA
Overcurrent protection	: 315 A gG
Rated load current (IL)	: 125 A
Follow current interrupt rating (Ifi)	: 3 kA at 350 Vac 25 kA at 264 Vac

Product data – type 16315 - C1 25-350

Plug	: one pole
Maximum continuous operating voltage (Uc)	: 350 Vac
Nominal discharge current (In)	: 25 kA
Impuls discharge current (Iimp)	: 25 kA

Product data – type 16316 - C2 40-350

Plug	: one pole
Maximum continuous operating voltage (Uc)	: 350 Vac
Nominal discharge current (In)	: 25 kA
Maximum discharge current (Imax)	: 40 kA

Product data – type 16317 - C1 Neutral-350

Plug	: one pole
Maximum continuous operating voltage (Uc)	: 350 Vac
Nominal discharge current (In)	: 100 kA
Impuls discharge current (Iimp)	: 100 kA

Product data – type 16329 - PRD1 25r 1P

Socket with plugs	: one pole with remote contact
Plugs	: 1 x C1 25-350 + 1 x C2 40-350
Maximum continuous operating voltage (Uc)	: 350 Vac
Nominal discharge current (In)	: 25 kA
Impuls discharge current (Iimp)	: 25 kA

Product data – type 16330 - PRD1 25r 1P+N

Socket with plugs	: two pole with remote contact
Plugs	: 1 x C1 25-350 + 1 x C2 40-350 + 1 x C1 Neutral-350
Maximum continuous operating voltage (Uc)	: 350 Vac
Nominal discharge current (In)	: L/N - 25 kA N/PE - 100 kA

Impuls discharge current (Iimp) : L/N - 25 kA
N/PE - 100 kA

Product data – type 16331 - PRD1 25r 3P

Socket with plugs : three pole with remote contact
Plugs : 3 x C1 25-350 + 3 x C2 40-350
Maximum continuous operating voltage (Uc) : 350 Vac
Nominal discharge current (In) : 25 kA
Impuls discharge current (Iimp) : 25 kA

Product data – type 16332 - PRD1 25r 3P+N

Socket with plugs : four pole with remote contact
Plugs : 3 x C1 25-350 + 3 x C2 40-350
+ 1 x C1 Neutral-350
Maximum continuous operating voltage (Uc) : 350 Vac
Nominal discharge current (In) : L/N - 25 kA
N/PE - 100 kA
Impuls discharge current (Iimp) : L/N - 25 kA
N/PE - 100 kA

TESTS**Test requirements**

EN 61643-11:2012
EN 61643-11:2012/A11:2018

Test result

The test results are documented in DEKRA test file 230314100.

Additional information

This certificate replaces certificate No. 2170677.01 which we hereby declare invalid.

Conclusion

The examination has confirmed that all requirements were met.

Factory locations

The factory locations are registered with the numbers 676000, 326192 and 87926.