

Clipsal Brand



ARGUS Presence detector High Frequency for High Bay - 2 channel



Version	Art. no.
	752HF2RC

Presence detector for ceiling mounting.

Functions:

- Presence detection via high frequency technology
- Lighting switches on and off automatically
- Quick and easy setting of the detection brightness, switching duration and sensitivity
- Detection range Ø 14 m at an installation height of 2.5 m
- Detection range Ø 10 m at an installation height of 10 m

Mains voltage: AC 220–240 V, 50/60 Hz

Nominal power:

Output 1:

- LED lamps: 100 W
- Incandescent lamps AC 230 V: 2000 W
- Halogen lamps AC 230 V: 1000 W
- Halogen with electronic transformer: 1000 VA
- Halogen with iron core transformer: 1000 VA
- Fluorescent tubes: 900 VA
- Compact fluorescent lamps: 100 W

Output 2:

- Relay switching capacity: AC 250 V, 5 A cosφ = 1
- Motor: 100 W

Upstream fuse: 10 A

Power consumption: < 1.5 W

Angle of detection: 360°

Range: Radius of max. 7 m (at 2.5-5 m mounting height)

Radius of max. 5 m (at 5.5-10 m mounting height)

Light sensor (sensitivity): 10–2000 Lux

Time setting:

Time 1: from approx. 10 s to approx. 30 min

Time 2: from approx. 10 s to approx. 60 min

Switching mode: Automatic

Connection: 3-wire, neutral conductor **required**

Operating temperature: at room temperature

IP protection rating: IP40 or IP52 depending on installation type

Colour: white

Dimensions (LxWxH):

Ø107 x 81 mm (flush mounted)

Ø107 x 53 mm (surface mounted)

Accessories: IR remote control for ARGUS Presence detector High Frequency 752RC/HF

IR remote control for ARGUS Presence detector High Frequency



Version	Art. no.
	752RC/HF

IR remote control for activating

- ARGUS Presence detector High Frequency for High Bay - 2 channel

Battery: CR2032

Range: up to 10 m

To be completed with: ARGUS Presence detector High Frequency for High Bay - 2 channel 752HF2RC



The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.